

### Features

- 3.0 x 2.6 mm footprint
- Smallest thickness with integrated actuator
- Extended life cycles
- IP68
- Ultra low current capabilities

### Typical Applications

- Mobile Phones
- Hearing Aids
- MP3 accessories
- Bluetooth Headset
- Automotive keyless entry system
- Smoke and CO detectors
- E-readers
- Home automation remote controls



### Specification

FUNCTION: momentary action, normally open

CONTACT ARRANGEMENT: 1 make contact = SPST, N.O.

TERMINALS: J lead type for SMT

### Mechanical

TRAVEL (mm): 0.15 ± 0.1

	Operating force Newtons (grams)	Tactile Feeling	Operating Life
KMT011NGJLHS	1.0 (100) ± 25%	≥ 10%	300,000
KMT021NGJLHS	1.6 (160) ± 25%	≥ 30%	300,000
KMT071NGJLHS	2.3 (230) ± 25%	≥ 30%	300,000
KMT031NGJLHS	3.4 (340) ± 25%	≥ 30%	300,000

	Operating force Newtons (grams)	Tactile Feeling	Operating Life
KMT012NGJLHS	1.0 (100) ± 25%	≥ 10%	1,000,000
KMT022NGJLHS	1.6 (160) ± 25%	≥ 30%	600,000
KMT072NGJLHS	2.3 (230) ± 25%	≥ 30%	600,000

### Electrical

MAXIMUM POWER:	0.5 VA
MAXIMUM VOLTAGE:	32 VDC
MINIMUM VOLTAGE:	20 mV
MAXIMUM CURRENT DC:	50 mA
MINIMUM CURRENT DC:	1 mA
DIELECTRIC STRENGTH:	≥ 250 Vrms (1mn)
CONTACT RESISTANCE:	≤ 150 mΩ
INSULATION RESISTANCE:	≥ 50 MΩ
BOUNCE TIME:	≤ 6 ms

### Environmental

OPERATING TEMPERATURE: -40°C to 85°C

STORAGE TEMPERATURE: -55°C (10 days) +85°C (4 days)

### Process

SOLDERING: This component is suited to the following methods:

- Lead free reflow soldering process in accordance with IEC 61760-1.

### Packaging

In reels of 5,000 pieces.


Dimensions of reels according to EIA 481B

External diameter 180 mm

**NOTE:** Specifications listed above are for switches with standard options.  
For information on specific and custom switches, consult Customer Service Center.

### Part Number Description

For any part number different from those listed above, please consult your local representative.




# KMT0 Series


## Nano-Miniature SMT Top Actuated

### Tactile Switches

Minimum actuator diameter is 1.0 mm. It is recommended to enlarge this diameter to a full flat surface covering the switch.



### TAPE & REEL



Dimensions are shown: mm  
Specifications and dimensions subject to change

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## C&K Switches:

[KMT011 NGJ LHS](#) [KMT021 NGJ LHS](#) [KMT031 NGJ LHS](#) [KMT071 NGJ LHS](#) [KMT012NGJLHS](#) [KMT022NGJLHS](#)  
[KMT072NGJLHS](#) [KMT023NGJLHG](#) [KMT031NGJLHS](#) [KMT021NGJLHS](#) [KMT013NGJLHG](#) [KMT 033 NGJ LHG](#)  
[KMT0D1NGJLHS](#) [KMT012 NGJ LHS](#) [KMT022 NGJ LHS](#) [KMT072 NGJ LHS](#)