

# KSC6 Series

## Sealed Tact Switch for SMT


KSC6 hard actuator 7,7 mm high



Type	Operating force FA (Newtons)	Operating life (operations)	Travel (mm)
KSC621	1.7 ± 0.5	300,000	0.4 ± 0.2
KSC631	2.55 ± 0.65	300,000	0.4 ± 0.2
KSC641	3.4 ± 0.85	300,000	0.4 ± 0.2

### Packaging


Switches delivered on continuous tape & reels of 950 pieces  
 Dimensions according to EIA RS-481/ IEC 60286-3 standard  
 External diameter 380 ± 2 mm



### How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

However, please note that all the combinations of these options are not feasible.  
 For any part number different from those listed above, please consult your local representative.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[KSC641G LFS](#) [KSC641J LFS](#) [KSC621J LFS](#) [KSC621GLFS](#) [KSC623JLFG](#) [KSC643JLFG](#) [KSC621JLFS](#)  
[KSC641JLFS](#) [KSC641GLFS](#) [KSC621G LFS](#) [KSC623J LFG](#) [KSC643J LFG](#)