


NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

© DENOTES CRITICAL CHARACTERISTICS.

CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE
----	---



COPIES TO			MATL SPEC			COPPER C1100					
1	9	18	FINISH TIN-PLATED								
2	10	19									
3	12	20									
4	13	21									
5	14	23	DRW	OPL	DATE	02/17/11	SCALE	FULL			
6	15	33	CHK		DATE		SUPER DR				
7	16	43	APPD		DATE		FINSH GOOD WT				
8	17	53					GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)											
DIMENSION		0.5 - 3		OVER UP TO	3 - 6	OVER UP TO	6 - 30	OVER UP TO	30 - 120	OVER UP TO	120 - 400
TOLERANCE		±0.05		±0.05		±0.1		±0.15		±0.2	
TITLE									BUS BAR FOR FLEX MEGA HOLDER		
3RD ANGLE PROJECTION											
			DES PLAINES, ILLINOIS 60016		REVISION		B		DRAWG. NO.		882-839-0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[882-839-5](#) [882-839-4](#) [882-839-2](#) [882-839-3](#)