

RELAY SOCKETS



99025 Socket



99026 Socket

Description

Available as Form A (SPST) or Form C (changeover SPDT), with no suppressor / resistor suppressor / diode suppressor, sealed or unsealed.

Features and Benefits

- Sockets dovetail together.
- Accepts standard quick connect terminals.
- Accept Littelfuse Heavy Duty and High Power Relays & standard ISO relays.
- Bracket for easy mounting.
- Rugged glass-filled polyamide.
- Weatherproof construction.
- Temperature range -40 °C to 85 °C

Heavy Duty and High Power Relays



HEAVY DUTY RELAYS	
RELAY	VOLTAGE
NO 40A	12V DC
NC 30A	12V DC
NO 20A	24V DC
NC 15A	24V DC

Applications

- 99025 - Use with Tyco (AMP) terminals 280756 or 280755
- 99026 - Use with Tyco (AMP) terminals 42281 or Ark-Les 3000H112A series

Web Resources

Download technical resources at:
littelfuse.com/RelaySockets

Ordering Information

PART NUMBER	DESCRIPTION
99025	Use with High Power Relays, Form A (SPST)
99026	Use with Heavy Duty Relays, Form A (SPST) or Form C (SPDT)

HIGH POWER RELAYS	
RELAY	VOLTAGE
NO 70A	12V DC
NC 60A	12V DC
NO 35A	24V DC
NC 30A	24V DC

Datasheet Replaces Hotfeed Number D-600

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[LFG480301CDINR](#) [99025](#) [99026](#)