



RTD ELEMENT RESISTANCE @ 0°C = 1,000 Ω ± 0.06%  
 RTD ELEMENT ACCURACY @ 0°C = ± 0.15°C  
 TCR = 3,850 ppm/°C  
 RTD ELEMENT ACCURACY CLASS = DIN EN 60751 F 0.15 (CLASS "A")  
 TEMPERATURE RATING = -70 TO +125°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	CLARIFIED ACCURACY CLASS INFO	08/11/17	DD
NONE	RELEASE TO PRODUCTION	10/16/13	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT	
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.	
DATE	10/16/13	714-639-1000 www.ussensor.com	
REV	"A"	Pt-RTD PROBE	
LAYER	0 OF 2	P/N USW3546	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[USW3546](#)