

MIN IN	
25	010
30	025
35	042
40	057
45	100
50	117
55	134
60	151

15/32-32NS

FACE NUT, KNURLED

HEX NUT

BLADE TERMINAL (2 PLACES)

ON

OFF

11.09

73.79 REF.

32.53 REF.

1.82 X .96 KEYWAY

12.70

DO NOT SCALE

LET	YEAR	DATE	BY	LET	YEAR	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVED	SCALE	DATE DRAWN
								PLB	PLB			4:1	8-28-56
								FINISH					DATE BLUEPRINT
								TOLERANCES					
								DECORAL ± MATING ±	TOGGLE SWITCH				55012
									A REDRAW				

11.09	237
12.70	500
23.79	937
37.58	1281
13.6	036
72	72

MSB.

15/32 - 32 NS

FACE NUT, KNURLED

HEX NUT

BLADE TERMINAL
(2 PLACES)

ON

OFF

11.09

RC ±

23.73

1.82 X .96' KEYWAY

METRIC

DO NOT SCALE

LET	WAS	DATE	BY LET	WAS	DATE	BY	MATERIAL #	DRAWN PJB	CHECKED	APPROVED	SCALE 1:1		DATE DRAWN 8-28-56
							FINISH #	CH. Cole Hersee Co. SOLELY ENGINEERING COMPANY INC. NEW YORK					DATE BLUEPRINT
							TOLERANCES DECIMAL ± METRIC ± .75	★ TOGGLE SWITCH					55013
			E	REDRAWN	10-19-57	G							

CH-188(4-78)

Confidential Property of Cole Hersee

MM	IN
1.25	0.10
9.52	375
10.92	420
11.93	470
12.70	500
13.20	520
14.28	562
16.18	631
17.53	629
0.26	0.38
1.82	0.72

HEX NUT, STEEL, ZINC PLT W/DICHROMATE DIP OR CAD PLT

KNURLED FACE NUT, BRASS, NICKEL PLT

BUSHING, 15/32-32 UNS-2A, BRASS, NICKEL PLT

SCREW, BRASS, 6-32 UNC-2A (2 REQ'D)

"ON"

"OFF"

REF

14.28

REF

32.53

182 X 096 KEYWAY

12.70

13.20

9.52

10.92

11.93

REF

26.18

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV'D	SCALE	DATE DRAWN	
								—H—	KR			11	7-27-50	
								FINISH	 Cole Hersee Co					DATE BLUEPRINT
							—H—							
				G	ADD SYMBOL	2/25/42	AF	TOLERANCES	TOGGLE SWITCH					5507
				F	REV & REDRAWN	12-3-79	RR	DECIMAL ± .010 METRIC ± .25						

Confidential Property of Cole Hersee

MAN IN

0.25	.010
0.50	.038
1.00	.072
2.00	.187
5.00	.437
10.00	.500
15.00	.625
20.00	.656
25.00	1.034
30.00	1.281

REF
M484

COLE-HERSEE CO.


6-32UNC-2A BRASS SCREW, 4.74 LG. (2 REQ'D)-

HEX NUT, STEEL, CADMIUM PLATE

KNURLED FACE NUT, BRASS, NICKEL PLT.

15/32 - 32 UNS-2A MTG
STEM, BRASS, NICKEL PLT.

-INSULATOR, BAKELITE



REF: MARINE M-484

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D.	SCALE	DATE DRAWN
								///	RM	 4-13-78		FULL	3 - 14 - 51
								FINISH ///	COLE-HERSEE COMPANY BOSTON, MASS. 02127, U.S.A.				DATE BLUEPRINT
				F	ECN 24601	10-2-78	BL	TOLERANCES FRACTIONAL $\pm$ DECIMAL ± 0.25	TOGGLE SWITCH				5558
				E	REDRAWN	4-3-78	UV						


SPAULDING CO., INC. 21-10961

Confidential Property of Cole Hersee

REF
M593

5568

COLE-HERSEE CO.




DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
									EA	TY 41277			11 29-66
								FINISH	COLE-HERSEE COMPANY				DATE BLUEPRINT
									BOSTON MASS 02127, U.S.A				
				C	ADDED DIM	5 14 87	1/2	TOLERANCES	TOGGLE SWITCH				5568
				B	RE DRAWN NO CHANGE	4 12 71	1/2	FRACTIONAL ± DECIMAL ±.015					

REF
M 584

COLE-HERSEE CO.




DO NOT SCALE

LE	WAS	DATE	BY	LET	WAS	DATE	BY	MATER L	DRAWN	CHECKED	APPR V D	SCALE	USED ON	D T E D A W N
								11	E A	R B		F U L L		1-28-52
								N S 11	COLE-HERSEE COMPANY BOSTON MASS 02127 USA					DATE B E P R
				F	DIM CHANGE ECN 23704	3-29-88	J K							
				E	KPMY DIM ADDED 17537	1-7-72	CT							
				D	REDRAWN REVISED	6-5-70	J B	O E A N C E UNLESS SPEC IED 2 DECIM L 010 3 DEC MA .006 ANGULAR 2°	NAME	TOGGLE SWITCH				P O 5570

MM. IN
 0.25 .010
 0.96 .038
 1.82 .072
 11.09 .437
 12.70 .500
 15.84 .625
 25.03 1.025
 31.87 1.255
 REF.

5558

M-484



METRIC



DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
									SN			1:1	3-17-50
								FINISH					DATE BLUEPRINT
				C	NICKEL PLATE / 21749	8-9-82							
				C1	.937 / C2 / 1.281								
				B	REDRAWN	12-11-79	VA	TOLERANCES DECIMAL $\pm$ METRIC $\pm .010$					
TOGGLE SWITCH													M-484

CH-188(4-78)

REF
5507

M 493



METRIC

DO NOT SCALE

LET		WAS		DATE	BY	LET		WAS		DATE	BY	MATERIAL #	DRAWN <i>R/S</i>	CHECKED DPS 8-19-82	APPR'D	SCALE 1:1	DATE DRAWN 7-60-54
												FINISH #	Cole Hersee Co. 70 OLD COH. AVE. SOUTH BOSTON MA U.S.A. 02127				DATE BLUEPRINT
			B ₁	NICKEL PLATED	21749	8-9-82	(B)	TOLERANCES									
			B ₁	K/D DRAWN #937	B ₂	1.281	8-9-82	(R) DECIMAL ± METRIC ±	TOGGLE SWITCH								M 493

CH-188(4-78)

Confidential Property of Cole Hersee

25	.010
96	.038
182	.072
11.09	.437
12.70	.500
25.03	1.025
152.40	6.000

TOGGLE, CHROME PLATE

BUSHING, CHROME PLATE, 15/32-32UNS

FACE NUT, CHROME PLATE

HEX NUT

ON

OFF

WIRE LEAD
152.40 LONG
(2 REQ'D)

11.09

REF

25.03

1.82 X .96 KEYWAY

12.70

METRIC


LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	DATE DRAWN
								H	EA	DP3 8-19-82		1:1	11-27-56
								FINISH	 Cole Hersee Co. 20 OLD COLONY AVENUE SOUTH BOSTON MA U.S.A. 02127				DATE BLUEPRINT
								H					
								TOLERANCES	TOGGLE SWITCH				M 584
								DECIMAL ± METRIC ±					
				B	REV REDRAWN	21749	8-9-82	(R)					

CH-188(4-78)

Confidential Property of Cole Hersee

25	.010
11.09	.437
12.70	.500
25.03	1.025
50.25	1.191
.96	.038
1.82	.072

M-586



METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	DATE DRAWN
								<u>H</u>	EA	DPS 8/19/82		1:1	11-27-56
								FINISH <u>H</u>	 Cole Hersee Co. 20 OLD COLONY AVENUE SOUTH BOSTON MA U.S.A. 02127				DATE BLUEPRINT
				B	PLATE/21749	8-9-82	(C)						
				B ₁	.937	B ₂	1.281						
				A	REDRAWN	10/19/81	(G)	TOLERANCES DECIMAL ± METRIC ± .75	TOGGLE SWITCH				M-586

CH-188(4-78)

Confidential Property of Cole Hersee

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[55013](#) [M-584](#) [M-484](#) [M-493](#)