

# PTS635 Series 3,5 mm Tact Switches

## Features/Benefits

- Compact size 6 x 3.5 mm
- Variety of switch heights
- Choice of actuation force
- RoHS compliant and compatible

## Typical Applications

- Consumer products
- Instrumentation
- Computer products
- Industrial



## Specification

FUNCTION: Momentary action  
CONTACT ARRANGEMENT: SPST, N.O.  
TERMINALS: PC pins

## Mechanical

ACTUATION FORCE: PTS635L models: 130 grams.  
PTS635H models: 200 grams.  
LIFE EXPECTANCY: 20,000 operations.

## Electrical

CONTACT RATING: 50 mA @ 12 V DC.  
DIELECTRIC STRENGTH: 250 V AC min.  
CONTACT RESISTANCE: 100 mΩ max. initial.  
INSULATION RESISTANCE: 10<sup>11</sup>Ω min.

## Environmental

OPERATING TEMPERATURE: -40°C to 60°C

**NOTE:** Specifications listed above are for switches with standard options.  
For information on specific and custom switches, consult Customer Service Center.

## Process

SOLDERING: Preheating to 100°C for 45 sec. max. Keep flux flush with top surface of PCB; do not apply to component side of PCB and area where terminals are located. Soldering to 255°C for 5 sec. max. Clean by brushing on solder surface. Do not clean switch with solvents.

## Materials

BASE: 6/6 nylon or glass filled polyester (PBT) (UL 94V-0).  
ACTUATOR: 6/6 nylon or polyacetal (UL 94HB).  
COVER PLATE: Tin plated stainless steel  
DOME CONTACTS: Phosphor bronze, silver clad.  
STATIONARY CONTACTS: Brass, silver plated.  
TERMINALS: Brass, silver plated. Insert molded.


## Packaging

Bulk packaging.

**Tape & reel for:**  
PTS635Sx43SMTR, 1700 pcs per reel

## How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.




\* SMTR only available with PTS635 43 Actuator Height options.

# PTS635 Series


## 3,5 mm Tact Switches

### THRU-HOLE




For "H" dimension please refer to chart on next page


#### PCB LAYOUT



### SMT




#### PCB LAYOUT



### ACTUATION FORCE


| OPTION CODE | FORCE     |
|-------------|-----------|
| <b>L</b>    | 130 grams |
| <b>H</b>    | 200 grams |

### ACTUATOR HEIGHT

| OPTION CODE | HEIGHT "H" or LENGTH "L" | TERMINATION     | SCHEMATIC                                                                                |
|-------------|--------------------------|-----------------|------------------------------------------------------------------------------------------|
| <b>43</b>   | 4,3 (.169)               | Thru-hole & SMT | 1  2 |
| <b>50</b>   | 5,0 (.197)               | Thru-hole       |                                                                                          |

### INSERTION TYPE

#### SMTR 43



DIRECTION OF FEED →



Dimensions are shown: mm  
Specifications and dimensions subject to change



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[PTS635SL43](#) [PTS635SL50](#) [PTS635VH39](#) [PTS635VL39 LFS](#) [PTS635SL25SMTR LFS](#) [PTS635SK25SMTR LFS](#)  
[PTS635VH39 LFS](#) [PTS635VH31 LFS](#) [PTS635VL31 LFS](#) [PTS635SL43 LFS](#) [PTS635SL43SMTR LFS](#) [PTS635SH43](#)  
[LFS](#) [PTS635SL50 LFS](#) [PTS635SK43SMTRLFS](#)