

Features/Benefits

- 2 axis, multi-direction operation
- 2,000,000 life cycle for toggle
- Center select momentary switch
- Small package size

Typical Applications

- Gaming peripherals
- Remote Control Vehicles
- Mini-joystick
- Thumb control
- Navigation control
- Industrial control
- Heavy equipment



Electrical

TOTAL RESISTANCE (POTENTIOMETERS): $10k\Omega \pm 20\%$ initial
Within $\pm 20\%$ of initial values for 10,000 cycles

RESISTANCE POTENTIOMETERS: Percentage of the voltage of terminal 1-2 to the voltage of terminal 1-3

RATED VOLTAGE: 50 VAC or 5 VDC

RATED POWER: 0.05 A @ 12 VDC

CONTACT NOISE: Noise < 10% of operating voltage

VOLTAGE DIVIDER: 39.6 ~ 60.4%

INSULATION RESISTANCE: > 100 M Ω

WITHSTANDING VOLTAGE: No arcing or breakdown

Mechanical

PATTERN OF ACTUATOR MOVEMENT: Toggle cross-wide and in a circle

FULL STROKE ACTUATION STOP STRENGTH: > 3.1 kgf
(3 seconds minimum)

PULL STRENGTH OF THE ACTUATOR: > 5.0 kgf
(3 seconds minimum)

ACTUATION FORCE: 120 +/- 50 gf (12 +/- 5mN*M of Torque)

ACCURACY OF RETURN TO ACTUATOR RELEASE POSITION: $\pm 3^\circ$

TOGGLE ANGLE OF OPERATION: 26° max. angle from vertical
through full circular range of rotation

OPERATING LIFE: 1,000,000 cycles minimum (center switch)
2,000,000 cycles minimum (thumbstick toggle)

Environment

OPERATING TEMPERATURE: -10°C to $+70^\circ\text{C}$


STORAGE TEMPERATURE: -30°C to $+80^\circ\text{C}$

Packaging


Tray (60 units)

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.



* Please note some option codes are mutually exclusive. Consult factory if you have any questions



First Angle
Projection

Dimensions are shown: mm
Specifications and dimensions subject to change

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[THB001P](#)