
# **'D'** SUBMINIATURE TECHNICAL SPECIFICATION

## PRINTED CIRCUIT BOARD **HOLE PATTERNS**

#### DIMENSIONAL INFORMATION


#### 9 WAY



Face view of plug & rear view of sacket





#### **15 WAY**





#### **25 WAY**






#### **37 WAY**





### 50 WAY





#### TERMINATION STYLES, OUTLINE DIMENSIONS AND MOUNTING DETAILS





Type R

90° right angled pins for flow soldering onto a printed circuit

#### Standard options available:

- 0 Economy 'D' fitted with stamped, gold plated contacts.
- Standard 'D' fitted with turned copper alloy contacts, O gold plated over nickel.
- O Five basic shell sizes containing 9, 15, 25, 37, and 50 contacts.
- 0 Provision for solder bucket, straight P.C.B., and 90° P.C.B. terminations.
- 0 Intermateable with MIL-C-24308.
- 0 Two part thermoplastic insulators, flame retardant to UL94VO.
- O Standard shell finish, yellow passivation over zinc plate.
- 0 Dimpled plug connector shells available to ensure good E.M.I. shielding.
- Ó Tin plated shells available, usually specified in conjunction with dimpled plug shells to enhance continuity.
- Ideal for use in business machines, computers, telecommunications and general instrumentation.

#### General Electrical and Mechanical Specification

**Current Rating:** 5A per contact with 20 A.W.G. cable **Working Voltage:** 500V AC or DC peak

Initial: <5 Milliohms Contact Resistance: Insulation Resistance: >10 Megohm. -55°C to 125°C Temperature Range: Polarisation: By tranezoidal shell Coupling:

By friction

Supplementary locking accessories

also available

Mating Cycles: 500

Materials and Finishes Shell:

Steel bright electro tin plated,

Insulators:

Two part thermoplastic mouldings,

flame retardent to UL94VO

Contacts: Copper alloy, gold plated over nickel.

#### DIMENSIONS - PANEL CUT OUT



SHELL SIZE	A-0.2	B±0.1	C-0.2	D±0.2	E±0.2	F±0.2	G±0.2	
9 WAY	30.8	25.0	12.4	22.4	13.0	20.5	11.4	
15 WAY	39.2	33.3	12.4	30.5	13.0	28,8	11.4	
25 WAY	53,1	47.0	12.4	44.3	13.0	42.5	11.4	
37 WAY	69.5	63.5	12.4	60.7	13.0	59.1	11.4	
50 WAY	67	61.1	15.4	58.3	15.8	56.3	14.1	

## SHELL DIMENSIONS





## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Lorlin:

SDP25Z SDP37Z SDP50Z SDS9Z SDS15Z SDS25Z SDS37Z SDS50Z SDP9Z SDP15Z