



PART NUMBER	LCD-A3X1C50TR/A	REV.	-
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.



CHARACTERISTICS	
FLUID TYPE	TN
BACKGROUND COLOR	GRAY
VIEWING DIRECTION	6:00
DISPLAY MODE	REFLECTIVE
OPERATING VOLTAGE	5.0V A.C.
OPERATING TEMP.	-40°C TO +105°C
STORAGE TEMP.	-40°C TO +105°C
DRIVING METHOD	STATIC
CONNECTION TYPE	40 PINS

PIN NO.	1	2	3	4	5	6	7	8	9	10
SEGMENT	COM	Y	K	N/C	N/C	N/C	N/C	DP1	1E	1D
PIN NO.	11	12	13	14	15	16	17	18	19	20
SEGMENT	1C	DP2	2E	2D	2C	DP3	3E	3D	3C	3B
PIN NO.	21	22	23	24	25	26	27	28	29	30
SEGMENT	3A	3F	3G	2B	2A	2F	2G	COL	1B	1A
PIN NO.	31	32	33	34	35	36	37	38	39	40
SEGMENT	1F	1G	N/C	N/C	N/C	N/C	OVER	LO BAT	X	COM

CHARACTER DETAIL



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[LCD-A3X1C50TR/A](#)