



ELECTRO-OPTICAL CHARACTERISTICS T _a =25°C V _f =12V AC/DC			
PARAMETER	MIN	TYP	MAX UNITS
INPUT VOLTAGE		12	V AC/DC
ENERGY USED		5	W
TOTAL LUMENS		315	LUMENS
VIEW ANGLE		24	2x theta
COLOR TEMPERATURE		3000	°K
COLOR RENDERING INDEX (CRI)	80		
OPERATING TEMPERATURE	-20		40 °C
LIFE HOURS		25000	HRS
EMITTED COLOR:	WHITE		
LENS FINISH:	WATER CLEAR		

UNCONTROLLED DOCUMENT

DATE: 12.02.11	DRAWN BY: AB
PAGE: 1 OF 1	CHKD BY: JD
SCALE: NTS	APRVD BY: DT
UNIT: mm [INCH]	(Rd)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSP-M16MW012C05](#)