





8		7		6		5		4		3		2		1	
W48- X - XX - X - X - X - X															
F		F													
E		E													
D		D													
C		C													
B		B													
A		A													

ROUND BEZEL

SQUARE BEZEL
(ONLY FOR BUSHING MONTING)




Ø3.3
LIGHT PIPE
LIGHTED SWITCH ONLY



RECOMMENDED P.C. BOARD HOLE PATTERN
(FOR PC TERMINAL)
COMPONENT SIDE




DETAIL OF TERMINAL POSITION

BUSHING MOUNT



REFERENCE
PANEL CUT-OUT
PANEL THICKNESS: 0.5-3mm

SNAP FIT MOUNT



RECOMMENDED
PANEL CUT-OUT
PANEL THICKNESS: 1.0mm , 2.0mm , 3.0mm±0.5

SWITCH ACTION	BUTTON TYPE	FP(mm)
MOMENTARY	ILLUMINATION LIGHT PIPE BUTTON	7.6±0.5
MAINTAINED	ILLUMINATION LIGHT PIPE BUTTON	6.0±0.5

DWG TYPE SALES DRAWING	DRAWN <i>K.Y.</i>	TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5 X.XX ± 0.25 ANGULAR ± 5°	DWG TITLE W48-MECHANICAL MOMENTARY/MAINTAINED, CENTER SPOT/POWER-STANDBY ILLUMINATION								
STATUS RELEASE	REVIEW		DWG NO. W48-E,F,G,H								
This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文作為安達電子電器股份有限公司之智慧財產，非經許可不得翻取、複製、轉變成其他形式使用或散佈	APPROVED <i>v.w.</i>	THIRD ANGLE PROJECTION 	■ 管制文件 □ 非管制文件				Unit mm	SCALE	REV 1	RoHS Compliant	SHEET 2 OF 3
	DATE 2010/3/11	REF: ---									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[W48-E-RB-R-BK-B](#) [W48-G-RB-G-BK-B](#)