



Mallory Sonalert Products, Inc.

Part #: **FL1M-8CJ-2**
8mm Panel Light

Sales Outline Drawing


Revision: **B**

Specifications:

Panel Hole	8 mm
Voltage Type	DC
LED Color Available	Red, Green, Blue, Yellow, or White
Lens Color	Same as LED
Rated Voltage Available	See table below
Max Current Draw	20 mA
Storage & Operating Temperature	-20 °C to +85 °C
Ingress Protection Rating	IP65
LED Life	70,000 hours
Weight (Typical)	4.9 g
Housing Material	Nickel-plated Brass, PA66, and Polycarbonate
Termination Type	Flat Blades Quick-Connect Terminal
Terminal Dimensions	2.8mm x 0.6mm
Max Nut Torque	13 ft-lbs (18 Nm)
Panel Thickness	0.04-0.24" (1-6 mm)
Hardware Kit	LM8-FSQ8-MHDP8

RoHS Compliant

Dimensions (mm):



Part Number:

FL1M-8CJ-2-X#V

B=Blue

G=Green

R=Red

Y=Yellow

W=White

Rated Voltage

Length for reference only.

	Light Intensity	Dominant Wavelength	Viewing Angle
Red	1000 -1500 mcd	622 nm	35°
Green	8000 -10000 mcd	522 nm	60°
Yellow	1000 -1500 mcd	590 nm	35°
Blue	2000 - 3000 mcd	464 nm	35°

Rated Voltage	2 VDC	3 VDC	6 VDC	12 VDC	24 VDC	48 VDC	110 VDC	220 VDC	380 VDC
Red	1.8-2.2V	2.7-3.3V	5.4-6.6V	10.8-13.2V	21.6-26.4V	43.2-52.8V	99-121V	198-242V	342-418V
Green	N/A	3-3.2V	5.4-6.6V	10.8-13.2V	21.6-26.4V	43.2-52.8V	99-121V	198-242V	342-418V
Blue	N/A	3.12-3.2V	5.4-6.6V	10.8-13.2V	21.6-26.4V	43.2-52.8V	99-121V	198-242V	342-418V
Yellow	2-2.2V	2.7-3.3V	5.4-6.6V	10.8-13.2V	21.6-26.4V	43.2-52.8V	99-121V	198-242V	342-418V
White	N/A	3-3.2V	5.4-6.6V	10.8-13.2V	21.6-26.4V	43.2-52.8V	99-121V	198-242V	342-418V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mallory Sonalert:

[FL1M-8CJ-2-R2V](#) [FL1M-8CJ-2-Y12V](#) [FL1M-8CJ-2-Y24V](#) [FL1M-8CJ-2-R110V](#) [FL1M-8CJ-2-Y2V](#) [FL1M-8CJ-3-G12V](#)
[FL1M-8CJ-2-G110V](#) [FL1M-8CJ-3-R110V](#) [FL1M-8CJ-3-Y110V](#) [FL1M-8CJ-3-Y24V](#) [FL1M-8CJ-2-G24V](#) [FL1M-8CJ-3-](#)
[G110V](#) [FL1M-8CJ-3-G24V](#) [FL1M-8CJ-2-G12V](#) [FL1M-8CJ-3-R12V](#) [FL1M-8CJ-2-R24V](#) [FL1M-8CJ-2-Y110V](#) [FL1M-](#)
[8CJ-3-Y2V](#) [FL1M-8CJ-3-G3V](#) [FL1M-8CJ-3-R24V](#) [FL1M-8CJ-2-R12V](#) [FL1M-8CJ-3-Y12V](#) [FL1M-8CJ-2-G3V](#) [FL1M-](#)
[8CJ-3-R2V](#)