


Threaded Pipe

Dimensions: mm

Assembly Procedure

Thread one side into base of unit and the other side into the J-MOUNTINGBRACKET.

Material: Stainless Steel SUS304

UL50, C22.2 No.94, NEMA Type 3R, 4X, & 12, and IP66 approved, RoHS compliant, Gasket.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[J-POLE-S](#)