


Sales Outline Drawing**Revision A****Specifications:**

Impedance (Ω)	$8 \pm 15\%$ at 2000 Hz at 1.0 V
Rated Power (W)	0.2
Max Power (W)	0.5
Frequency Range (Hz)	Fo ~ 20000
Resonance Freq Fo (Hz)	$1500 \pm 20\%$ at 1.0V
Output S.P.L. (dB)	87 ± 3 at 0.2w/0.1m 2k, 2.5k, 3k, 4.0kHz 74 ± 3 at 1w/1m 2k, 2.5k, 3k, 4.0kHz
Magnet Size (mm)	$\varnothing 6.5 \times 1.5$
Magnet	Nd-Fe-B
Frame Material	PBT +20% glass (Black)
Operating Temp	-20 to 55°C
Weight (g)	2.0
Options	For other options contact factory

Dimensions: ± 0.5 (units: mm)**ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-1715PK](#)