




**Specifications: May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Impedance (Ω)	$8 \pm 15\%$ at 2000 Hz at 1.0 V
Rated Power (W)	0.1
Max Power (W)	0.15
Resonance Freq Fo (Hz)	$1500 \pm 20\%$ at 1.0V
Frequency Range (Hz)	Fo ~ 6000
Output S.P.L. (dB)	88 ± 3 at 0.1w/0.1m 2k, 2.5k, 3k, 4.0kHz 77 ± 3 at 1w/1m 2k, 2.5k, 3k, 4.0kHz
Magnet Size (mm)	$\varnothing 6.5 \times 1.5$
Magnet	Rare
Frame Material	ABS UL-94HB (Black)
Operating Temp	-20 to 55°C
Weight (g)	3.2
Options	For other options contact factory

Dimensions: ± 0.3 (units: mm)

ROHS Compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-2315PK](#)