


Sales Outline DrawingRevision **B**

May not be suitable for all medical and aerospace applications.
Specifications: Contact Mallory Sonalert to discuss your application.

Impedance (Ω)	$8 \pm 15\%$ at 1500 Hz at 1.0V
Rated Power (W)	0.3
Max Power (W)	0.5
Resonance Freq Fo (Hz)	$1200 \pm 20\%$ at 1.0V
Frequency Range (Hz)	Fo ~ 20000
Output S.P.L. (dB)	86 ± 3 at .3w/.1m 1.0k, 1.2k, 1.5k, 2.0kHz 72 ± 3 at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Magnet Size (mm)	$\varnothing 5.3 \times 1.0$
Magnet	Nd-Fe-B
Frame Material	Metal
Operating Temp	-20 to 55°C
Weight (g)	0.6
Options	For other options contact factory

Dimensions: ± 0.2 (units: mm)**ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PSR10N08AK](#)