

**Mallory Sonalert Products, Inc.**

Part #:

SBT5GLPC**Sales Outline Drawing**


Revision:

E**Specifications:****cUL Recognized to IEC60601-1-8 AMD2:2020
Any Melody - Low Priority Only**

Sound Level Category:	Loud
Mode of Operation:	Low Priority Alarm - 2 beeps repeating every 20 sec
Voltage Rating:	2.7 to 5.5 VDC
Frequency:	150 to 4000 Hz
Loudness @ 10cm:	85 to 95 dB(A) Typ.
Average Current Draw:	<35mA Typ.
Ipk Current*:	300mA
Housing Material:	ABS 777D Plastic Resin, Black
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight Typical:	0.6 oz (17g)
Options:	Please contact factory.
Condition by wave solder (°C)	260 ± 5 within 5 sec
Condition by hand solder (°C)	350 ± 20 within 5 sec

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

PATENT NUMBER: 7880593



*Ipk = Instantaneous Peak

tolerances:

±0.01 [±0.3]

±0.005 [±0.1]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SBT5GLPC](#)