

**Mallory Sonalert Products, Inc.**


Part #:

SCE028XD3MG3B**Sales Outline Drawing**

Revision:

C**Specifications:**

Sound Level Category:	Extra Loud	Extra Loud	Extra Loud	Loud
Mode of Operation:	Continuous	Double Pulse	Quick Pulse	Dual Tone
Loudness @ 2 FT:	95 to 105 dB(A) Typ.	95 to 105 dB(A) Typ.	95 to 105 dB(A) Typ.	85 to 95 dB(A) Typ.
Pulse Rate (PPS):	N/A	2	60	7
Frequency:	2900 ± 500 Hz	2900 ± 500 Hz	2900 ± 500 Hz	3.0 - 2.9 kHz
Connection:	T-BLOCK ONLY	T-BLOCK; BLACK WIRE TO (-)	T-BLOCK; YELLOW WIRE TO (-)	T-BLOCK; BOTH WIRES TO (-)
Voltage Rating:	16 to 28 VDC			
Current Draw:	40mA MAX			
Housing Material:	6/6 Nylon, Color: Black			
Storage Temperature:	-40° to +85° C			
Operating Temperature:	-40° to +85° C			
Panel Mounting:	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.			
Knurled Nut:	Used to attach part to panel. The max recommended torque is 10 in-lbs.			
Weight (Typical):	1.6 oz (45g)			
NEMA 3R,4X, & 12:	Approved with use of ACC03.			
cUL Recognition:	cUL Recognized			
Options:	Please contact factory.			

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SCE028XD3MG3B](#)