


**Mallory Sonalert Products, Inc.**Part #: **SCE048LD3VC4B****Sales Outline Drawing**Revision: **A****Specifications:**

Sound Level Category:	Loud	Medium	Soft	
Mode of Operation:	Slow Pulse	Slow Pulse	Slow Pulse	
Pulse Rate (PPS):	1	1	1	
Loudness @ 2 FT:	85 to 95 dB(A) Typ.	75 to 85 dB(A) Typ.	65 to 75 dB(A) Typ.	
Frequency:	2900 \pm 500 Hz	2900 \pm 500 Hz	2900 \pm 500 Hz	
Connection:	T-BLOCK ONLY	T-BLOCK; BLUE WIRE TO (-)	T-BLOCK; YELLOW WIRE TO (-)	
Voltage Rating:	28 to 48 VDC			
Current Draw:	40mA MAX			
Housing Material:	6/6 Nylon, Color: Black			
Storage Temperature:	-40° to +85° C			
Operating Temperature:	-40° to +85° C			
Panel Mounting:	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.			
Knurled Nut:	Used to attach part to panel. The max recommended torque is 10 in-lbs.			
Weight (Typical):	1.6 oz (45g)			
NEMA 3R,4X, & 12:	Approved with use of ACC03.			
cUL Recognition:	cUL Recognized			
Options:	Please contact factory.			

Dimensions: Inches (mm)**ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SCE048LD3VC4B](#)