


Specifications:

Description	Speaker-housing assembly designed to meet the requirements of IEC60601-1-8
Coil Impedance	8Ω @ 1-Volt
Rated Wattage	0.25 Watts (4Vpp Sine Wave, 176mA)
Max Wattage	0.5 Watts
Recommended Drive Frequency	300 ± 24 Hz, results in a 900 Hz fundamental frequency
Sound Level	75dB @ 2ft (90dB @ 10cm) typical
Harmonics Present	4 harmonic peaks within ±15dB from 1 – 4 kHz
Housing	Nylon 6/6 (Color: Black)
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	1.5 oz (42 g)
Options	For other options contact factory

Dimensions: Inches (mm)
RoHS Compliant


Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SCS300MDS](#) [SCS300MDB](#)