


Specifications:

Sound level Category	Medium Sound Level
Mode of Operation	Continuous
Mounting	Panel (see note A)
Voltage Rating	1 – 5 Vdc
Frequency	2900 Hz \pm 500 Hz
Loudness (Min. Voltage)	55 dB(A) min. @ 2 FT and 1 Vdc
Loudness (Max Voltage)	68 dB(A) min. @ 2FT and 5 Vdc
Current Draw	3 mA Max @ 1 Vdc
Current Draw	12 mA Max @ 5 Vdc
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	0.5 oz (17 g)
Housing	6/6 Nylon, Color Black
Options	For other options contact factory

RoHS Compliant**Dimensions:** Inches (mm)

NOTE A:
MOUNTING - THIS PORTION
SNAP-LOCKS INTO PANELS 1/32" TO
1/8" THICK USING APPROPRIATE
COMPRESSION WASHER.
1.063 \pm 0.005 DIA. PANEL HOLE REQ'D.



NOTE B:
TERMINALS - .016 BRASS, HOT TIN FINISH WITH
.076 WIRE HOLE. TERMINAL WILL ACCEPT
STANDARD 1/8" QUICK CONNECT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SNP2R](#)