

Sales Outline Drawing


Revision A

Specifications:

Voice Coil Impedance (Ω)	$8 \pm 15\%$ at 800 Hz 1.0 V
Rated Input (W)	0.5
Max. Input (W)	1.0
Lowest Resonance Freq F_o (Hz)	$600 \pm 20\%$
Frequency Range (Hz)	$F_o \sim 4000$
Output S.P.L. (dB)	92 ± 3 at 1W 1M .8k, 1k, 1.2k, 1.5kHz
Magnet Size (mm)	$\varnothing 12.5 * 1.5$
Magnet	Nd-Fe-B
Core Material Mylar	Mylar
Frame Material	Metal
Operation / Storage Temp	-20 to 55°C
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PSR-57N08A01-AQ](#)