



Mallory Sonalert Products, Inc.

Part #: **SCE016MD3MV0W10**

Sales Outline Drawing


Revision: **A**

Specifications:

Sound Level Category:	Medium	Soft	Soft	Loud
Mode of Operation:	Continuous	Continuous	Continuous	Continuous
Pulse Rate (PPS):				
Loudness @ 2 FT:	82 dB(A) Typ. @ 12 VDC	60 dB(A) Typ. @ 12 VDC	71 dB(A) Typ. @ 12 VDC	95 dB(A) Typ. @ 12 VDC
Frequency:	2900 ± 500 Hz	2900 ± 500 Hz	2900 ± 500 Hz	2900 ± 500 Hz
Connection:	RED (+); BLACK (-)	RED (+); BLACK & YELLOW (-)	RED (+); BLACK & BLUE (-)	RED (+); BLACK & YELLOW AND BLUE (-)
Voltage Rating:	6 to 16 VDC			
Current Draw:	40mA MAX			
Housing Material:	6/6 Nylon, Color: Black			
Storage Temperature:	-40° to +85° C			
Operating Temperature:	-40° to +85° C			
Panel Mounting:	Recommended hole size is 1.25" (31.75mm). Thread front will fit standard 30mm (1.181") hole.			
Knurled Nut:	Used to attach part to panel. The max recommended torque is 10 in-lbs.			
Weight (Typical):	1.6 oz (45g)			
NEMA 3R, 4X, & 12:	Approved with use of ACC03.			
cUL Recognition:	cUL Recognized			
Options:	Please contact factory.			

Dimensions: Inches (mm)

ROHS Compliant



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SCE016MD3MV0W10](#)