

**Specifications:**


|                         |                                    |
|-------------------------|------------------------------------|
| Sound level Category    | Medium Sound Level                 |
| Mode of Operation       | Fast Pulse                         |
| Mounting                | Panel (see note B)                 |
| Voltage Rating          | 60 to 250 Vac/dc                   |
| Frequency               | 2900 Hz $\pm$ 500 Hz               |
| Loudness (Min. Voltage) | 68 dB(A) min. @ 2 FT and 60 Vac/dc |
| Loudness (Max Voltage)  | 78 dB(A) min. @ 2FT and 250 Vac/dc |
| Current Draw            | 4 mA Max @ 60 Vac/dc               |
| Current Draw            | 13 mA Max @ 250 Vac/dc             |
| Min. Pulse Rate (PPS)   | 2 @ 60 Vac/dc                      |
| Max. Pulse Rate (PPS)   | 10 @ 250 Vac/dc                    |
| Duty Cycle (%)          | 50 (Approx)                        |
| Storage Temperature     | -40°C to +85°C                     |
| Operating Temperature   | -30°C to +65°C                     |
| Weight (Typical)        | 2.7 oz (76 g)                      |
| Housing                 | 6/6 Nylon, Color Black             |
| Options                 | For other options contact factory  |

**Dimensions:** Inches (mm)

**UL Recognized**


PART DIMENSIONS BEFORE CODE DATE 0810 5

PART DIMENSIONS AFTER CODE DATE 0811 1



NOTE A: TERMINALS--032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING-- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1/25" HOLE PUNCHED IN PANEL. IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.



NOTE A: TERMINALS--032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING-- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1/25" HOLE PUNCHED IN PANEL. IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SC250P](#)