

	<b>E480232</b>
---	----------------

**Features**

- Low Zener Impepance
- High Temp Soldering: 260°C for 10 Seconds At Terminals
- Unidirectional And Bidirectional
- For Bidirectional Devices Add "C" To The Suffix Of The Part Number: i.e. P4KE6.8CA for 5% Tolerance Devices
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Moisture Sensivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant (Note1) ("P" Suffix Designates RoHS Compliant. See Ordering Information)

**Mechanical Data**

- Polarity :Color Band Denotes Cathodes Except Bipolar
- Mounting Position :Any
- Weight :0.012ounce,0.3grams

**Maximum Ratings**

- Operating Junction Temperature Range: -55°C to +175°C
- Storage Temperature Range: -55°C to +175°C

Peak Pulse Power Dissipation	$P_{PPM}$	400W	$T_A=25^\circ C$
Steady State Power Dissipatoin	$P_{M(AV)}$	1 W	$T_L=75^\circ C$
Response Time	Unidirectional $<1 \times 10^{-12}$ Seconds;		
	Bidirectoinal $<5 \times 10^{-9}$ Seconds		

Note:1.High Temperature Solder Exemption Applied, see EU Directive Annex 7a.

Pin Configuration:



**400WATTS TVS  
6.8 to 550 VOLTS**

**DO-41**



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.160	0.205	4.10	5.20	
B	0.080	0.107	2.00	2.70	$\phi$
C	0.028	0.035	0.71	0.90	$\phi$
D	1.000	-----	25.40	-----	

**Electrical Characteristics @ 25°C Unless Otherwise Specified**

MCC Part Number		Breakdown Voltage $V_{(BR)}@I_T$ (Volts)		TEST Current $I_T$	Reverse Standoff Voltage $V_{WM}$	Maximum Reverse Leakage $I_R@V_{WM}$	Maximum Clamping Voltage $V_C@I_{PP}$	Maximum Peak Pulse Current ( $I_{PP}$ )	Maximum Temperature Coefficient Of $V_{(BR)}$
Uni-Polar	Bi-Polar	Min	Max	mA(DC)	V	$\mu A$	V	A	(%/°C)
P4KE6.8A	P4KE6.8CA	6.45	7.14	10	5.8	1000	10.5	39	0.057
P4KE7.5A	P4KE7.5CA	7.13	7.88	10	6.4	500	11.3	36.3	0.061
P4KE8.2A	P4KE8.2CA	7.79	8.61	10	7.02	200	12.1	33.9	0.060
P4KE9.1A	P4KE9.1CA	8.65	9.55	1	7.78	50	13.4	30.6	0.068
P4KE10A	P4KE10CA	9.5	10.5	1	8.55	10	14.5	28.3	0.073
P4KE11A	P4KE11CA	10.5	11.6	1	9.4	5	15.6	26.3	0.075
P4KE12A	P4KE12CA	11.4	12.6	1	10.2	5	16.7	24.6	0.078
P4KE13A	P4KE13CA	12.4	13.7	1	11.1	1	18.2	22.5	0.081
P4KE15A	P4KE15CA	14.3	15.8	1	12.8	1	21.2	19.3	0.084
P4KE16A	P4KE16CA	15.2	16.8	1	13.6	1	22.5	18.2	0.086
P4KE18A	P4KE18CA	17.1	18.9	1	15.3	1	25.5	16.1	0.088
P4KE20A	P4KE20CA	19	21	1	17.1	1	27.7	14.8	0.090
P4KE22A	P4KE22CA	20.9	23.1	1	18.8	1	30.6	13.4	0.092
P4KE24A	P4KE24CA	22.8	25.2	1	20.5	1	33.2	12.3	0.094
P4KE27A	P4KE27CA	25.7	28.4	1	23.1	1	37.5	10.9	0.096
P4KE30A	P4KE30CA	28.5	31.5	1	25.6	1	41.4	9.9	0.097
P4KE33A	P4KE33CA	31.4	34.7	1	28.2	1	45.7	9	0.098
P4KE36A	P4KE36CA	34.2	37.8	1	30.8	1	49.9	8.2	0.099
P4KE39A	P4KE39CA	37.1	41	1	33.3	1	53.9	7.6	0.100
P4KE43A	P4KE43CA	40.9	45.2	1	36.8	1	59.3	6.9	0.101
P4KE47A	P4KE47CA	44.7	49.4	1	40.2	1	64.8	6.3	0.101
P4KE51A	P4KE51CA	48.5	53.6	1	43.6	1	70.1	5.8	0.102
P4KE56A	P4KE56CA	53.2	58.8	1	47.8	1	77	5.3	0.103
P4KE62A	P4KE62CA	58.9	65.1	1	53	1	85	4.8	0.104
P4KE68A	P4KE68CA	64.6	71.4	1	58.1	1	92	4.5	0.104
P4KE75A	P4KE75CA	71.3	78.8	1	64.1	1	103	4	0.105
P4KE82A	P4KE82CA	77.9	86.1	1	70.1	1	113	3.6	0.105
P4KE91A	P4KE91CA	86.5	95.5	1	77.8	1	125	3.3	0.106
P4KE100A	P4KE100CA	95	105	1	85.5	1	137	3	0.106
P4KE110A	P4KE110CA	105	116	1	94	1	152	2.7	0.107
P4KE120A	P4KE120CA	114	126	1	102	1	165	2.5	0.107
P4KE130A	P4KE130CA	124	137	1	111	1	179	2.3	0.107
P4KE150A	P4KE150CA	143	158	1	128	1	207	2	0.108
P4KE160A	P4KE160CA	152	168	1	136	1	219	1.9	0.108
P4KE170A	P4KE170CA	162	179	1	145	1	234	1.8	0.108
P4KE180A	P4KE180CA	171	189	1	154	1	246	1.7	0.108
P4KE200A	P4KE200CA	190	210	1	171	1	274	1.5	0.108
P4KE220A	P4KE220CA	209	231	1	185	1	328	1.3	0.108
P4KE250A	P4KE250CA	237	263	1	214	1	344	1.2	0.110
P4KE300A	P4KE300CA	285	315	1	256	1	414	1	0.110
P4KE350A	P4KE350CA	332	368	1	300	1	482	0.85	0.110
P4KE400A	P4KE400CA	380	420	1	342	1	548	0.75	0.110
P4KE440A	P4KE440CA	418	462	1	376	1	602	0.68	0.110
P4KE480A	P4KE480CA	456	504	1	408	1	658	0.61	0.110
P4KE510A	P4KE510CA	485	535	1	434	1	698	0.57	0.110
P4KE530A	P4KE530CA	503.5	556.5	1	477	1	725	0.55	0.110
P4KE540A	P4KE540CA	513	567	1	459	1	740	0.54	0.110
P4KE550A	P4KE550CA	522.5	577.5	1	495	1	760	0.52	0.110

Note: For bidirectional type having  $V_{WM}$  of 10 volts and less, the  $I_R$  limit is double.  
For parts without A, the  $V_{BR}$  is  $\pm 10\%$

### Curve Characteristics

Fig. 1 - Peak Pulse Power Rating Curve



Fig. 2 - Typical Junction Capacitance



Fig. 3 - Pulse Waveform



Fig. 4 - Pulse Derating Curve



## Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel: 5Kpcs/Reel
(Part Number)-AP	Ammo Packing: 5Kpcs/Ammo Box
(Part Number)-BP	Bulk: 1Kpcs/Box, 50Kpcs/Carton

Note : Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Micro Commercial Components (MCC):

[P4KE480A-TP](#) [P4KE12A-TP](#) [P4KE200CA-TP](#) [P4KE6.8A-TP](#) [P4KE9.1CA-TP](#) [P4KE100A-TP](#) [P4KE400CA-TP](#)  
[P4KE440CA-TP](#) [P4KE220CA-TP](#) [P4KE350A-TP](#) [P4KE15A-TP](#) [P4KE15CA-TP](#) [P4KE300A-TP](#) [P4KE540A-TP](#)  
[P4KE20A-TP](#) [P4KE110CA-TP](#) [P4KE180A-TP](#) [P4KE220A-TP](#) [P4KE540CA-TP](#) [P4KE6.8CA-TP](#) [P4KE18A-TP](#)  
[P4KE200A-TP](#) [P4KE180CA-TP](#) [P4KE91CA-TP](#) [P4KE440A-TP](#) [P4KE300CA-TP](#) [P4KE13A-TP](#) [P4KE18CA-TP](#)  
[P4KE120A-TP](#) [P4KE75CA-TP](#) [P4KE7.5A-TP](#) [P4KE130CA-TP](#) [P4KE400A-TP](#) [P4KE39A-TP](#) [P4KE11A-TP](#)  
[P4KE11CA-TP](#) [P4KE120CA-TP](#) [P4KE12CA-TP](#) [P4KE130A-TP](#) [P4KE13CA-TP](#) [P4KE150A-TP](#) [P4KE150CA-TP](#)  
[P4KE160A-TP](#) [P4KE160CA-TP](#) [P4KE16A-TP](#) [P4KE16CA-TP](#) [P4KE170A-TP](#) [P4KE170CA-TP](#) [P4KE20CA-TP](#)  
[P4KE22A-TP](#) [P4KE22CA-TP](#) [P4KE24A-TP](#) [P4KE24CA-TP](#) [P4KE250A-TP](#) [P4KE100CA-TP](#) [P4KE110A-TP](#)  
[P4KE250CA-TP](#) [P4KE27A-TP](#) [P4KE27CA-TP](#) [P4KE30CA-TP](#) [P4KE33A-TP](#) [P4KE33CA-TP](#) [P4KE350CA-TP](#)  
[P4KE36A-TP](#) [P4KE36CA-TP](#) [P4KE39CA-TP](#) [P4KE43A-TP](#) [P4KE43CA-TP](#) [P4KE47A-TP](#) [P4KE47CA-TP](#)  
[P4KE480CA-TP](#) [P4KE510A-TP](#) [P4KE510CA-TP](#) [P4KE51A-TP](#) [P4KE51CA-TP](#) [P4KE530A-TP](#) [P4KE530CA-TP](#)  
[P4KE550A-TP](#) [P4KE550CA-TP](#) [P4KE56A-TP](#) [P4KE56CA-TP](#) [P4KE62A-TP](#) [P4KE62CA-TP](#) [P4KE68A-TP](#)  
[P4KE68CA-TP](#) [P4KE7.5CA-TP](#) [P4KE75A-TP](#) [P4KE8.2A-TP](#) [P4KE8.2CA-TP](#) [P4KE82A-TP](#) [P4KE82CA-TP](#)  
[P4KE9.1A-TP](#) [P4KE91A-TP](#) [P4KE100CA-AP](#) [P4KE100CA-BP](#) [P4KE10A-AP](#) [P4KE10A-BP](#) [P4KE10CA-AP](#)  
[P4KE10CA-BP](#) [P4KE110A-AP](#)