









# MHSS Series

## Microminiature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
<p><b>Contact ratings:</b> 300 mA at 6 VDC</p> <p><b>Initial contact resistance:</b> 60 milliohms max.</p> <p><b>Insulation resistance:</b> 100 megohms min. at 100 VDC</p> <p><b>Dielectric strength:</b> 100 VAC for 1 minute</p> <p><b>Electrical life:</b> 5000 cycles min.</p> <p><b>Operating temperature range:</b> -20°C to +70°C</p> <p><b>Solder heat resistance:</b> 350°C max. for 3 seconds</p> <p><b>Washing not recommended</b></p>	<ul style="list-style-type: none"> <li>Excellent tactile feed-back (detent action).</li> <li>Molded-in terminals minimize flux or solder entry.</li> <li>Ultra-compact case size.</li> <li>Low profile.</li> </ul>
MATERIALS	
<p><b>Contacts &amp; terminals:</b> Silver plated</p> <p><b>Case:</b> 30% Glass filled nylon, type 6/6, black</p> <p><b>Actuator:</b> Nylon, type 6/6, black (blue for MHSS2220 only)</p>	

MODEL NO.			
<b>MHSS1104</b>			
 <p>VERTICAL ACTUATOR</p>	<p><b>1P2T</b></p>  <p>● = COMMON</p>	 <p>MECHANICAL OUTLINE</p>	 <p>P.C. BOARD LAYOUT</p>
<b>MHSS1105</b>			
 <p>RIGHT ANGLE ACTUATOR</p>	<p><b>1P2T</b></p>  <p>● = COMMON</p>	 <p>MECHANICAL OUTLINE</p>	 <p>P.C. BOARD LAYOUT</p>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[MHSS1104A](#) [MHSS1105A](#) [MHSS1104](#) [MHSS1105](#) [MHSS2220](#)