

B series

15A and 25A terminal posts

ELECTRICAL SPECIFICATIONS

- Dielectric strength :
15A type : 3.000 Vrms 50 Hz min. between shaft and panel
25A type : 4.000 Vrms 50 Hz min. between shaft and panel
- Short overload (< 2mn) : 50 % with cable lug

MATERIALS

- Shaft : brass, nickel plated
- Insulated nut : ABS molding over brass
- Other insulated parts : phenolic resin or melamine

GENERAL SPECIFICATIONS

- Terminal connection by :
 - plug Ø 4 mm (.157)
 - solder lug terminals,
 - wire lead
- Operating temperature : -40°C to +70°C

Dimensions : first dimensions are in mm while inches are shown as bracketted numbers.



Packaging unit : 100 pieces or multiple per type and colour.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[B12](#)