

2600 series

Illuminated and non-illuminated rocker switches

Distinctive features and specifications



- ☐ Three rocker shapes : plain, V-shaped or concave
- ☐ Various rocker colours
- ☐ Frame with protection guard on 2600LP models
- ☐ UL, CSA, VDE and NF (EN 61058-1) approved

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load and approved ratings : see table below.
- Initial contact resistance : 10mΩ max. at 1A 2VDC
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength : 2.500 Vrms 50 Hz min. between terminals
3.000 Vrms 50 Hz min. between terminals and metal panel
- Electrical life : 10.000 cycles at full load

FUNCTIONS	APPROVED RATINGS				DIRECT CURRENT	
	CSA	UL	VDE	NF	24 VDC	12 VDC
	CSA 22-2	UL 1054	EN 61058-1	EN 61058-1		
ON - OFF ON - ON	1/6 HP 125VAC 16A 125VAC 16A 250VAC 1/3 HP 250VAC	1/6 HP 125VAC 16A 125VAC 16A 250VAC 1/3 HP 250VAC	10(4)A 250VAC T 85/55	-	10A	15A
ON - OFF - ON	10A 125VAC 10A 250VAC 1/6 HP 125/250VAC	10A 125VAC 10A 250VAC 1/6 HP 125/250VAC	LI option 10(4)A 250VAC	LI option 10(4)A 250VAC	8A	10A
ON - ON - ON	-	-	-	-	5A	8A
OTHERS	10A 125VAC 10A 250VAC 1/6 HP 250VAC	-	LI option 10(4)A 250VAC	LI option 10(4)A 250VAC	8A	10A

MATERIALS

- Case : melamine/polyester
- Frame : polyamide
- Actuator : polyamide
- Contacts :
A : silver
C : copper, silver plated

GENERAL SPECIFICATIONS

- Panel thickness : 0,8 mm to 4 mm (.031 to .157)
- Operating temperature :
- silver contacts (A) : -20°C to +125°C
- silver plated contacts (C) : -10°C to +55°C

AGENCY APPROVALS



EN 61058-1 EN 61058-1

Availability : consult factory for details of approved models.


Marking : approved models are standard marked.

2600 series

Illuminated and non-illuminated rocker switches

Overview

MODEL
STRUCTURE



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boot U2150 available to protect the switches against dust and water. See section H.




NOTICE : please note that not all combinations of above numbers are available.
Refer to the following pages for further information.



2600 series

Illuminated and non-illuminated rocker switches

Overview




Packaging unit : 20 pieces per type and colour.

2600 series


Illuminated and non-illuminated rocker switches

MODEL
STRUCTURE




- Model 2600LP with protection guard
- 1 and 2 pole configurations


2640LH



2640LH/2



MODEL
STRUCTURE



2600LH - single pole



Screw term.
+ clamp




2631LH
2636LH
2639LH

Solder lug/
quick-connect

2631LH/2
2636LH/2
2639LH/2

III	II	I
A2-A1	A2-A3	
B5-B4	B5-B6	

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON



2600LH - double pole



Screw term.
+ clamp




2641LH
2644LH*
2645LH
2646LH
2647LH
2648LH
2649LH

Solder lug/
quick-connect

2641LH/2
2644LH/2*
2645LH/2
2646LH/2
2647LH/2
2648LH/2
2649LH/2

III	II	I
A2-A1	A2-A3	
B5-B4	B5-B6	

III	II	I
ON	-	OFF
ON	ON	ON
MOM	-	ON
ON	-	ON
MOM	OFF	MOM
ON	OFF	MOM
ON	OFF	ON



* Function 4 : SP in DP case, see end of catalogue.

2600LP - with protection guard - single pole



Screw term.
+ clamp




2631LP
2636LP
2639LP

Solder lug/
quick-connect

2631LP/2
2636LP/2
2639LP/2

III	II	I
A2-A1	A2-A3	
B5-B4	B5-B6	

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON





2600 series

Illuminated and non-illuminated rocker switches

2600LP - with protection guard - double pole




Screw term.
+ clamp


Solder lug/
quick-connect

		III	II	I
2641LP	2641LP/2	A2-A1	A2-A3	
2644LP*	2644LP/2*	B5-B4	B5-B6	
2645LP	2645LP/2	ON	-	OFF
2646LP	2646LP/2	ON	ON	ON
2647LP	2647LP/2	MOM	-	ON
2648LP	2648LP/2	ON	-	ON
2649LP	2649LP/2	ON	-	ON
		ON	-	ON
		MOM	OFF	MOM
		ON	OFF	MOM
		ON	OFF	ON

* Function 4 : SP in DP case, see end of catalogue.




PANEL CUT-OUT



TERMINAL OPTION

Specify after LH or LP.

/3 Normalized quick-connect terminals 6,35 x 0,8 (.250 x .031)




2600 series

Illuminated and non-illuminated rocker switches


OPTIONS
● ● ●

CONTACT MATERIALS



- A** Silver
C Copper, silver plated (available with functions 1, 6 and 9 only)

FRAME COLOURS





- 1** Blue
1/4 Dark blue
2 Black (standard)
4 Grey
7/1 White
8 Chrome plated
B Light brown
E Dark brown




This option has UL approval only.


ROCKER SHAPES



1
Plain



2
V-shaped



3
Concave



2600 series

Illuminated and non-illuminated rocker switches

ROCKER COLOURS



For illuminated switches

	Without rocker	Blue*	Green*	Yellow	Red	White	Orange
Plain rocker P/N	-	U881	U883	U885	U886	U887	U889
V-shaped rocker P/N	-	U861	U863	U865	U866	U867	U869
Concave rocker P/N	-	U871	U873	U875	U876	U877	U879
Colour code	0	1	3	5	6	7/1	9

* With green or blue rocker, use fluorescent lamp only.

For non-illuminated switches or switches with illuminated window (•)


	Without rocker	Light brown	Dark brown	Beige	Blue	Dark blue	Black	Green	Grey	Yellow	Red	White	Orange
Plain rocker P/N	-	U1250B	U1250BF	U1250	U1251	U1251/4	U1252	U1253	U1254	U1255	U1256	U1257	U1259
V-shaped rocker P/N	-	U1270B	U1270BF	U1270	U1271	U1271/4	U1272	U1273	U1274	U1275	U1276	U1277	U1279
Concave rocker P/N	-	U1260B	U1260BF	U1260	U1261	U1261/4	U1262	U1263	U1264	U1265	U1266	U1267	U1269
Colour code	0	02	04	03	10	14	20•	30•	40	50	60•	70	90

Complete box with one of above colour codes.

To order rockers separately, use their P/N (U....) and complete box with code 0.

Rockers with illuminated windows (codes 20, 30, 60) : part numbers on request.

ROCKER MARKING



MARKING		4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3	3 6 1 4	4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3	4 1 5 2 6 3
COLOUR	-	6 3	6 3	6 3	6 3	6 3	6 3	1 4	6 3	6 3	6 3	6 3
Black	00	01	02	06	07	08	03	04	05*	40	43*	46
Red	00	11	12	16	17	18	13	14	15*	41	44*	47
White	00	21	22	26	27	28	23	24	25*	42	45*	48

* Not available on V-shaped rockers


Special markings and marking on rockers with illuminated window : consult factory.

2600 series


Illuminated and non-illuminated rocker switches

OPTIONS
● ● ●

LAMP



L0	Non-illuminated switch
L6V	Filament lamp 6V
L12V	Filament lamp 12V
L24V	Filament lamp 24V
L110V	Neon lamp 110VAC
L110V1	BLUE fluorescent lamp 110VAC
L110V3	Green fluorescent lamp 110VAC
L220V	Neon lamp 220VAC
L220V1	BLUE fluorescent lamp 220VAC
L220V3	Green fluorescent lamp 220VAC
L380V	Neon lamp 380VAC
L380V1	BLUE fluorescent lamp 380VAC
L380V3	Green fluorescent lamp 380VAC
LI	EN61058-1 approved version without lamp (3 position switches)




For illuminated models, the lamp is always connected between center terminals 2 and 5.



Lamps L380V, L380V1 and L380V3 are not UL/CSA approved.

D


ILLUMINATED WINDOW



For black, green and red rockers only

/3 Green
/6 Red

With green, use fluorescent lamp only.
No marking available on illuminated windows.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[2641LH/2A21600L220V](#)