

PBA series

Piezo switches

Distinctive features - Specifications - Overview

- ☐ Sealed to IP 68 (switches mounted on panel)
- ☐ Easy to clean metal surface
- ☐ Long life
- ☐ Ring or dot illumination

ELECTRICAL SPECIFICATIONS

- Rated voltage : 5V to 24 VAC/DC max.
- Rated current : 0,2A to 1A max.
- Switch resistance ON : 10Ω max.
- Switch resistance OFF : 5MΩ min.
- Switch capacitance : 25pF
- LED : 20mA 5VDC

GENERAL SPECIFICATIONS

- Operating force : 2 to 6N
- Life expectancy : 50 million cycles
- Operating temperature : -40°C to +75°C
- EMC compatibility according to EN 61058-1 for the whole range
- EMC compatibility according to EN 61000-4 & EN61000-6-2 for model 1A (code 002)
- Sealing : IP 68 per IEC 529 (switches mounted on panel)

MATERIALS

- Case : aluminium, anodized or stainless steel
- Terminals : multi-wire leads AWG24, length 300 mm (11.81)


Standard hardware supplied :

1 hex nut U4116 (19 mm ac. flats) or
1 hex nut U6440 (25 mm across flats)

Packaging unit :

Bushing Ø 16 (.629) : 40 pieces
Bushing Ø 22 (.866) : 20 pieces

Dimensions : first dimensions are in mm while inches are shown as bracketted numbers.




NOTICE : please note that not all combinations of above numbers are available.
Refer to the following pages for further information.

PBA series


Piezo switches

Bushing Ø 16 (.629) - illuminated and non-illuminated



- Panel cut-out : Ø 16,2 mm (.637)
- Operator Ø 18 mm (.708)


MODEL
STRUCTURE



With illuminated ring



Flat operator
PBAR1AF




Wire colours : red : contact, yellow : LED anode (+), blue : LED cathode (-)

Non-illuminated



Flat operator
PBAR1AF

With chamfer
PBAR5AF



CASE COLOURS / MATERIALS



0 : natural anodized aluminium - 1 : blue anodized alum. - 2 : black anodized alum. - 3 : green anodized alum.
5 : gold anodized alum. - 6 : red anodized alum. - 9 : stainless steel (non-illum. only)

LED COLOURS




Blank : non-illuminated

A0B : blue - A0G : green - A0S : red - A0Y : amber

PBA series

Piezo switches


Bushing Ø 22 (.866) - illuminated and non-illuminated



Illuminated Non-illuminated

- Panel cut-out : Ø 22,2 mm (.874)
- Operator Ø 28 mm (1.102)

MODEL STRUCTURE




Wire colours : red : contact, yellow : LED anode (+), blue : LED cathode (-)

With illuminated dot



Flat operator
PBAR2AF

With chamfer
PBAR6AF




Non-illuminated



Flat operator
PBAR2AF

With chamfer
PBAR6AF



CASE COLOURS / MATERIALS



0 : natural anodized aluminium - 1 : blue anodized alum. - 2 : black anodized alum. - 3 : green anodized alum.
5 : gold anodized alum. - 6 : red anodized alum. - 9 : stainless steel (non-illum. only)

LED COLOURS



Blank : non-illuminated

LOB : blue - LOG : green - LOS : red - LOY : amber - LSG : red/green

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[PBAR2AF0000LSG](#)