

Date Last Revised: 10-31-06



Colors: Natural or Black
 Flexibility, Fits Holes of any Shape or Size
 Available from Stock in Coils of 100 ft.
 Material: Polyethylene

Polyethylene grommets are a lightweight low cost material good for general indoor applications. Polyethylene is not affected by ordinary solvents and resistant to abrasion.

Continuous Flexible Grommets can be used for round, square, and irregular shaped panels. Flexible grommets are attached quickly and easily using no special tools. In addition to protecting routed cables, wires, tubing, and other objects from chafing or unnecessary cuts, the installed grommet also puts an attractive finished touch to a product. Continuous flexible grommets are manufactured to fit over a range of panel thickness from .040 / .070" to .187 / .187". Sheet form materials can include glass, sheet metal, and wood. In many cases flexible grommets will grip the panel tightly and remain in place. Should the panel thickness vary to a point that the grommet will not adhere tightly by itself, the problem can usually be corrected by a touch of epoxy to keep the grommet tightly in place.

Serrated

Part Number	Dimensions: in.				
	Panel Range	Gap Ref	A Ref	B Ref	C Ref
561-FGSP0100B	.100/.120	0.095	0.045	0.12	0.22
561-FGSP0100N	.100/.120	0.095	0.045	0.12	0.22
561-FGSP0125B	.115/.125	0.112	0.04	0.125	0.22
561-FGSP0125N	.115/.125	0.112	0.04	0.125	0.22
561-FGSP0187B	.182/.187	0.18	0.05	0.187	0.275
561-FGSP0187N	.182 / .187	0.18	0.05	0.187	0.275
561-FGSP0400B	.040/.070	0.035	0.028	0.072	0.19
561-FGSP0400N	.040/.070	0.035	0.028	0.072	0.19
561-FGSP0520B	.045/.070	0.04	0.028	0.072	0.19
561-FGSP0520N	.045/.071	0.04	0.028	0.072	0.19
561-FGSP0620B	.055/.075	0.05	0.04	0.08	0.2
561-FGSP0620N	.055/.075	0.05	0.04	0.08	0.2
561-FGSP0850B	.080/.085	0.075	0.04	0.085	0.19
561-FGSP0850N	.080/.085	0.075	0.04	0.085	0.19

Uncut

Part Number	Dimensions: in.				
	Panel Range	Gap Ref	A Ref	B Ref	C Ref
561-FGUP0100B	.100/.120	0.095	0.045	0.12	0.22
561-FGUP0100N	.100/.120	0.095	0.045	0.12	0.22
561-FGUP0125B	.115/.125	0.112	0.04	0.125	0.22
561-FGUP0125N	.115/.125	0.112	0.04	0.125	0.22
561-FGUP0187B	.182/.187	0.18	0.05	0.187	0.275
561-FGUP0187N	.182/.187	0.18	0.05	0.187	0.275
561-FGUP0400B	.040/.070	0.035	0.028	0.072	0.19
561-FGUP0400N	.040/.070	0.035	0.028	0.072	0.19
561-FGUP0520B	.045/.070	0.04	0.028	0.072	0.19
561-FGUP0520N	.045/.070	0.04	0.028	0.072	0.19
561-FGUP0620B	.055/.075	0.05	0.04	0.08	0.2
561-FGUP0620N	.055/.075	0.05	0.04	0.08	0.2
561-FGUP0850B	.080/.085	0.075	0.04	0.085	0.19
561-FGUP0850N	.080/.085	0.075	0.04	0.085	0.19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-FGSP0850N](#) [561-FGSP0850B](#) [561-FGSP0125N](#) [561-FGSP0125B](#) [561-FGSP0400B](#) [561-FGSP0400N](#) [561-FGSP0187N](#) [561-FGSP0187B](#) [561-FGSP0100N](#) [561-FGSP0100B](#) [561-FGSP0520B](#) [561-FGSP0520N](#) [561-FGSP0620N](#) [561-FGUP0620N](#) [561-FGSP0620B](#) [561-FGUP0187B](#) [561-FGUP0100B](#) [561-FGUP0100N](#) [561-FGUP0620B](#) [561-FGUP0850B](#) [561-FGUP0850N](#) [561-FGUP0187N](#) [561-FGUP0400N](#) [561-FGUP0400B](#) [561-FGUP0520N](#) [561-FGUP0520B](#) [561-FGUP0125N](#) [561-FGUP0125B](#) [561-FGUP0125B-SPL](#) [561-FGUP0125N-SPL](#) [561-MF250](#) [561-MM250](#) [561-FGUP0520B-SPL](#) [561-FGUP0520B-SPL](#)