


NEW ENGLAND SEMICONDUCTOR

BIPOLAR PNP TRANSISTOR TO-3

PACKAGE	DEVICE TYPE	V _{CEO} (sus) VOLTS	I _C (max) AMPS	h _{FE} @ I _C / V _{CE} (min/max @ A/V)	V _{CE(sat)} @ I _C /I _B (V @ A/A)	P _D * WATTS	f _T (MHz)
PNP TO-3 	2N3789	60	10	25-90@1/2	1@4/4	150	4
	2N3790	80	10	25-90@1/2	1@4/4	150	4
	2N3791^	60	10	50-150@1/2	1@5/5	150	4
	2N3792^	80	10	50-150@1/2	1@5/5	150	4
	2N4398	40	30	15-60@15/2	2@20/2	200	4
	2N4399^	60	30	15-60@15/2	2@20/2	200	4
	2N4901	40	5	20-80@1/2	1.5@5/1	87.5	4
	2N4902	60	5	20-80@1/2	1.5@5/1	87.5	4
	2N4903	80	5	20-80@1/2	1.5@5/1	87.5	4
	2N5683^	60	50	15-60@25/2	1@25/2.5	300	2
	2N5684^	80	50	15-60@25/2	1@25/2.5	300	2
	2N5745^	80	20	15-60@10/2	2@20/4	200	2
	2N5875	60	10	20-100@4/4	1@5/5	150	4
	2N5876	80	10	20-100@4/4	1@5/5	150	4
	2N5879	60	15	20-100@6/4	1@7/7	160	4
	2N5880	80	15	20-100@6/4	1@7/7	160	4
	2N5883	60	25	20-100@10/4	1@15/1.5	200	4
	2N5884	80	25	20-100@10/4	1@15/1.5	200	4
	2N6246	60	15	20-100@7/4	1.3@7/7	125	6
	2N6247	80	15	20-100@6/4	1.3@6/6	125	6
	2N6329	60	30	6-30@30/4	1.5@15/2	200	3
	2N6330	80	30	6-30@30/4	1.5@15/2	200	3
	2N6331	100	30	6-30@30/4	1.5@15/2	200	3

* T_C = 25°C

^Available in JAN, JANTX, JANTXV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[2N5883](#) [2N5880](#) [2N5884](#) [2N6330](#) [2N4901](#) [2N4903](#) [2N4398](#) [2N6329](#) [2N5876](#) [2N5879](#) [2N5875](#)