



 **CRESCENT**
Lufkin®

**Shockforce™ and Shockforce
Nite Eye™ G2 Tape Measures**

Trusted by the Trades.



SHOCKFORCE™ G2 AND SHOCKFORCE™ G2 NITE EYE

New Shockforce G2 and Shockforce G2 Nite Eye tapes have wider, thicker blades for a full 17-foot reach and a new blade barrier coating for 3X the blade life, but there's more: They have a bolstered case and fastening points, plus dual steel guardrails on both sides of the lock button – all for superior impact protection. They've been 120-foot drop tested for extreme durability. That means they're not just the best performing tapes we've ever made ... they're also the toughest.

DROP
120
FOOT
TESTED

Bolstered Case and Fastening Points

120' drop tested for extreme durability



New Improved Belt Clip

Features an integrated lever that opens the clip slightly for easier attachment and release from a tool belt



Wider, Thicker Blade

Two-sided with 2X larger print and vertical markings on back

TRI-LAYER TOUGH 3X BLADE LIFE

Tether Capable

Integrated thru-hole can be used as a tether loop attachment point when working at height or as a pivot for scribing arcs

Blade Barrier Coating

3x the blade life on the first 6"

Nested Diamond-Coated Endhook

Features 360-degree grasping power and nests flush with tape case for ultimate durability

A Tape For Every Job



Shockforce G2

New G2 tapes have a wider, thicker blade for a full 17 feet of reach so measuring jobs get done faster



Shockforce G2 Auto-Lock

New G2 Auto-Lock tapes stay locked when extended, retracting only when the release button is pushed



Shockforce G2 Magnetic

New G2 Magnetic tapes are perfect for measuring metal studs or drop ceiling grids and can double as a pick-up tool



L1225-02



L1225BAL-02



LM1225-02

Item No	Description	Shelf Pack Quantity	UPC	Shelf Pack Code	Product Package Dimensions	Product Weight
L1216-02	Gen 2 Shockforce Tape Measure, 16'	4	037103360861	10037103360868	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
LM1216-02	Gen 2 Shockforce Tape, Magnetic, 16'	4	037103359247	10037103359244	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
L1216CME-02	Gen 2 Shockforce Tape, CME, 16'/5M	4	037103359261	10037103359268	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
L1225-02	Gen 2 Shockforce Tape Measure, 25'	4	037103357946	10037103357943	2.7"L x 4.6"W x 7.6"H	1.21 lbs..
LM1225-02	Gen 2 Shockforce Tape Measure, 25', MAG	4	037103357960	10037103357967	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225AL-02	Gen 2 Shockforce Tape Measure, 25', AUTO	4	037103357953	10037103357950	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225CME-02	Gen 2 Shockforce, CME, 26'/8M	4	037103359308	10037103359305	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
LM1225CME-02	Gen 2 Shockforce, MAG, CME, 26'/8M	4	037103359353	10037103359350	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225ALCME-02	Gen 2 Shockforce, Autolock CME, 26'/8M	4	037103359322	10037103359329	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1235-02	Gen 2 Shockforce Tape, 35'	4	037103359360	10037103359367	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
LM1235-02	Gen 2 Shockforce Tape, Magnetic, 35'	4	037103359377	10037103359374	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
L1235CME-02	Gen 2, Shockforce, CME, 33'/10M	4	037103359407	10037103359404	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
LM1235CME-02	Gen 2 Shockforce Tape, MAG, CME, 33'/10M	4	037103359384	10037103359381	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
L1216B-02	Gen 2 Nite Eye Tape Measure, 16'	4	037103357977	10037103357974	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
LM1216B-02	Gen 2 Nite Eye Tape, Magnetic, 16'	4	037103359254	10037103359251	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
L1216CMEB-02	Gen 2 Nite Eye, CME, 16'/5M	4	037103359278	10037103359275	2.5"L x 3.9"W x 7.3"H	1.09 lbs.
L1225B-02	Gen 2 Nite Eye Tape Measure, 25'	4	037103357984	10037103357981	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
LM1225B-02	Gen 2 Nite Eye, Magnetic, 25'	4	037103359285	10037103359282	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225BAL-02	Gen 2 Nite Eye, Autolock 25'	4	037103359292	10037103359299	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225CMEB-02	Gen 2 Nite Eye, CME, 26'/8M	4	037103359315	10037103359312	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
LM1225CMEB-02	Gen 2 Nite Eye, MAG, CME, 26'/8M	4	037103359346	10037103359343	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1225ALCMEB-02	Gen 2 Nite Eye, Autolock CME, 26'/8M	4	037103359339	10037103359336	2.7"L x 4.6"W x 7.6"H	1.21 lbs.
L1235B-02	Gen 2 Nite Eye Tape Measure, 35'	4	037103360878	10037103360875	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
LM1235B-02	Gen 2 Nite Eye Tape Measure, 35', MAG	4	037103357991	10037103357998	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
L1235CMEB-02	Gen 2 Nite Eye, CME, 33'/10M	4	037103359414	10037103359411	2.7"L x 4.6"W x 7.6"H	1.56 lbs.
LM1235CMEB-02	Gen 2 Nite Eye, MAG, CME, 33'/10M	4	037103359391	10037103359398	2.7"L x 4.6"W x 7.6"H	1.56 lbs.

*17 foot standout based on maximum performance.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apex Tool Group:

[L1216B-02](#) [L1216CME-02](#) [L1216CMEB-02](#) [L1225-02](#) [L1225AL-02](#) [L1225ALCME-02](#) [L1225ALCMEB-02](#) [L1225B-](#)
[02](#) [L1225BAL-02](#) [L1225BSET2V-02](#) [L1225CME-02](#) [L1225CMEB-02](#) [LM1216-02](#) [LM1216B-02](#) [LM1225-02](#)
[LM1225B-02](#) [LM1225CME-02](#) [LM1225CMEB-02](#) [LM1235-02](#) [LM1235B-02](#) [LM1235CME-02](#) [LM1235CMEB-02](#)
[L1216-02](#)