



Circular Saw Blades



 **CRESCENT®**

Trusted by the Trades.

Circular Saw Blades

Crescent now offers a full range of professional circular saw blades designed to outlast and outperform. Premium laser cut blades featuring precision blend teeth, optimized tooth geometries and Active Shield™ protective blade coating deliver increased performance for the toughest applications on the jobsite.

8X BLADE LIFE
High Impact™ Premium Carbide Teeth

70% MORE CUTS PER CHARGE
Active Shield™ Protective Blade Coating

RESISTS NAILS ON IMPACT
Anti-Nail Kickback Tooth Design

PROTECTS AGAINST GUMMING AND CORROSION
Active Shield™ Protective Blade Coating

MINIMAL BLADE VIBRATION
FOR STRAIGHTER CUTS
Laser Cut Vibration Slots

REDUCES BLADE WARPING
Laser Cut Expansion Slots



NAILSLICER™ Framing Blades

- 8X Blade Life High Impact™ Premium Carbide Teeth
- 70% More Cuts Per Charge Active Shield™ Protective Blade Coating

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBFR-518	5-3/8"	18	Framing	20mm†	ATB	18°	.063"
CSBFR-524	5-3/8"	24	Framing	20mm†	ATB	18°	.063"
CSBFR-5518	5-1/2"	18	Framing	20mm†	ATB	18°	.063"
CSBFR-5524	5-1/2"	24	Framing	20mm†	ATB	18°	.063"
CSBFR-618	6-1/2"	18	Framing	5/8" with Diamond Knock-Out	ATB	18°	.063"
CSBFR-624*	6-1/2"	24	Framing	5/8" with Diamond Knock-Out	ATB	18°	.063"
CSBFR-724**	7-1/4"	24	Framing	5/8" with Diamond Knock-Out	ATB	18°	.063"
CSBFR-824	8-1/4"	24	Framing	5/8" with Diamond Knock-Out	ATB	18°	.094"

*CSBFR-624 is also available in a 10 Piece Bulk Pack

**CSBFR-724 is also available in a 2 Piece, 3 Piece and 10 Piece Bulk Pack

† With 10mm, 5/8" & 1/2" Reduction Rings

Demolition Blades

- 10X Blade Life Extreme Impact™ Premium Carbide Teeth
- Powers Through Tough Materials Anti-Kickback Tooth Design

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBFD-624	6-1/2"	24	Demolition	5/8" with Diamond Knock-Out	ATB+R	16°	.063"
CSBFD-724	7-1/4"	24	Demolition	5/8" with Diamond Knock-Out	ATB+R	16°	.063"



FINECUT™ Finishing Blades

- 10X Blade Life Extended Life and Durability
- 40% Smoother Surface Finish Precision™ Premium Carbide Teeth

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBFF-640	6-1/2"	40	Fine Finish	5/8" with Diamond Knock-Out	ATB	15°	.063"
CSBFN-740*	7-1/4"	40	Finishing	5/8" with Diamond Knock-Out	ATB	15°	.063"
CSBUF-760	7-1/4"	60	Ultra Fine Finish	5/8" with Diamond Knock-Out	ATB	15°	.063"
CSBFN-840	8-1/4"	40	Finishing	5/8" with Diamond Knock-Out	ATB	15°	.094"
CSBFF-860	8-1/2"	60	Fine Finish	5/8"	ATB	15°	.094"
CSBFF-1060	10"	60	Fine Finish	5/8"	Hi-ATB	15°	.094"
CSBUF-1080	10"	80	Ultra Fine Finish	5/8"	ATB	15°	.098"
CSBUL-1090	10"	90	Ultimate Fine Finish	5/8"	ATB	10°	.091"
CSBFF-1280	12"	80	Fine Finish	1"	Hi-ATB	7°	.118"
CSBUF-1290	12"	90	Ultra Fine Finish	1"	ATB	10°	.098"
CSBUL-12100	12"	100	Ultimate Fine Finish	1"	ATB	7°	.098"
CSBFF-1484	14"	84	Fine Finish	1"	ATB	15°	.118"

*CSBFN-740 is also available in a 10 Piece Bulk Pack

STEELSLICER™ Metal Cutting Blades

- 20X Blade Life Heat Defense™ Premium Cermet Teeth
- 40% Cooler Cuts Active Shield™ Protective Blade Coating

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBMM-530	5-3/8"	30	Medium Metal	20mm†	M-ATB	2°	.063"
CSBMM-5530	5-1/2"	30	Medium Metal	20mm†	M-ATB	2°	.063"
CSBMN-756	7-1/4"	56	Thin Metal	5/8" with Diamond Knock-Out	M-ATB	2°	.079"
CSBMM-748	7-1/4"	48	Medium Metal	5/8" with Diamond Knock-Out	M-ATB	2°	.079"
CSBMK-842	8"	42	Thick Metal	5/8"	M-ATB	2°	.079"

† With 10mm, 5/8" & 1/2" Reduction Rings

Aluminum Blades

- 2X Blade Life High Velocity™ Premium Carbide Teeth
- 2X Faster Cuts Active Shield™ Protective Blade Coating

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBAM-550	5-3/8"	50	Medium Aluminum	20mm†	TCG	5°	.094"
CSBAM-760	7-1/4"	60	Medium Aluminum	5/8" with Diamond Knock-Out	TCG	5°	.098"
CSBAK-756	7-1/4"	56	Thick Aluminum	5/8" with Diamond Knock-Out	TCG	5°	.098"
CSBAK-1060	10"	60	Thick Aluminum	5/8"	TCG	5°	.110"
CSBAM-1084	10"	84	Medium Aluminum	5/8"	TCG	5°	.110"
CSBAN-10100	10"	100	Thin Aluminum	5/8"	TCG	5°	.110"
CSBAM-1296	12"	96	Medium Aluminum	1"	TCG	5°	.110"
CSBAN-12120	12"	120	Thin Aluminum	1"	TCG	5°	.110"

† With 10mm, 5/8" & 1/2" Reduction Rings



General Purpose, Ripping & Combination Blades

- **10X Blade Life** *Micro Grain™ Premium Carbide Teeth*
- **Protects Against Gumming And Corrosion** *Active Shield™ Protective Blade Coating*

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBGN-840	8-1/2"	40	General Purpose	5/8" with Diamond Knock-Out	ATB	15°	.094"
CSBRP-1024	10"	24	Ripping	5/8"	ATB	15°	.098"
CSBGN-1040	10"	40	General Purpose	5/8"	ATB	15°	.098"
CSBCM-1050	10"	50	Combination	5/8"	ATB	15°	.094"
CSBGN-1244	12"	44	General Purpose	1"	ATB	15°	.098"
CSBCM-1260	12"	60	Combination	1"	ATB	15°	.118"

Composite Decking Blades

- **50% Smoother Finish** *Razor Tipped™ Premium Carbide Teeth*
- **Clean, Melt-Free Cuts** *Precision Triple Chip Grind (TCG)*

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBTX-744	7-1/4"	44	TREX®, Composite Decking, Cellular PVC	5/8" with Diamond Knock-Out	TCG	-3°	.063"
CSBTX-1072	10"	72		5/8"	TCG	-3°	.102"
CSBTX-1284	12"	84		1"	TCG	-3°	.102"

Fiber Cement Blades

- **75X Blade Life** *Premium Polycrystalline Diamond Teeth (PCD)*
- **Clean Cuts With 50% Less Dust** *Ultra-Thin Kerf Design*

Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBFC-704	7-1/4"	4	HardiePlank™ Siding, HardieTrim™ Board, Fiber Cement	5/8" with Diamond Knock-Out	Flat Top	10°	.071"
CSBFC-1006	10"	6		5/8"	Flat Top	10°	.087"
CSBFC-1208	12"	8		1"	Flat Top	10°	.094"

Laminate Flooring Blades

- **75X Blade Life** *Premium Polycrystalline Diamond Teeth (PCD)*
- **Clean, Accurate Cuts** *Ultra-Thin Kerf Design*


Item No.	Diameter	Tooth Count	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBLF-708	7-1/4"	8	Pergo™ Flooring, Engineered Flooring, Laminate Flooring, Bamboo, Hardwood	5/8" with Diamond Knock-Out	Flat Top	10°	.071"
CSBLF-1012	10"	12		5/8"	Flat Top	10°	.087"
CSBLF-1216	12"	16		1"	Flat Top	10°	.094"

Wood & Metal Blades

- **10X Blade Life** *Ultra Hardened™ Premium Carbide Teeth*
- **Fast, Clean Cuts** *Thin Kerf Design*

Item No.	Dia.	Tooth Ct.	Application	Arbor	Tooth Grind	Hook Angle	Kerf
CSBWM-632	6-1/2"	32	Softwood, Hardwood, Plywood, OSB, Steel Studs, Angle Iron, Threaded Rod	5/8" with Diamond Knock-Out	ATB	5°	.067"
CSBWM-736	7-1/4"	36		5/8" with Diamond Knock-Out	ATB	5°	.067"

For more information on Crescent Circular Saw Blades, visit www.crescenttool.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apex Tool Group:

[CSBRP-1024](#) [CSBTX-1072](#) [CSBTX-1284](#) [CSBTX-744](#) [CSBTX-744-09](#) [CSBUF-1080](#) [CSBUF-1290](#) [CSBUF-760](#)
[CSBUL-1090](#) [CSBUL-12100](#) [CSBWM-632](#) [CSBWM-736](#)