



- BGA/QFP Rework Systems
- T0058755782

Thermocouple Type K, Ø 0, 1 mm

Product no.: T0058755782

Dimensions L x W x H (mm)	---
Dimensions L x W x H (inches)	---
Weight (approx.) in kg	---
Voltage	---
Power	---
Channels	---
Temperature range (depends on tool) °C	-200 - 1250
Temperature range (depends on tool) °F	-328 - 2282
Temperature accuracy °C	1.1°C
Temperature accuracy °F	+/- 1.1°C
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[T0058755782](#)