

WAD101N

Product no.: WAD101N



Benefits





Technical Data

Dimensions L x W x H (mm)	175 x 135 x 102
Dimensions L x W x H (inches)	6,89 x 5,31 x 4,02
Weight (approx.) in kg	2.4
Voltage	120 V / 60 Hz
Power	105 W
Channels	1
Temperature range (depends on tool) °C	50 - 450 (550)
Temperature range (depends on tool) °F	122 - 842 (999)
Temperature accuracy °C	± 9 (30)
Temperature accuracy °F	± 17 (50)
Temperature stability °C	± 2
Temperature stability °F	± 5
Equipotential bonding socket	Via a 3.5 mm jack bush (initial state-hard-grounded)
Display	---
Air consumption l/min	10
Operating pressure in bar/psi	4/58
Capacity l/min	max. 10
Vacuum	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[WAD101N](#)