

WR5000M

5-channel, hot air, desoldering, soldering rework system (700 W)
Product no.: WR5000MN



Benefits

- 700 watts of power over 5 independently-controlled channels
- Specified tips included
- Application flexibility with up to 19 tool options (WR3ME only)
- PC Connectivity and data logging software included (WR3ME only)
- Note: Not applicable with WRK kit or WVP vacuum
- ECO button for "Sleep Mode"



Technical Data

Dimensions L x W x H (mm)	280 x 240 x 103
Dimensions L x W x H (inches)	11,02 x 9,45 x 4,06
Weight (approx.) in kg	7.3
Voltage	120 V
Power	700 W
Channels	3
Temperature range (depends on tool) °C	93 - 500
Temperature range (depends on tool) °F	200 - 850
Temperature accuracy °C	±9°C
Temperature accuracy °F	±17°F
Temperature stability °C	±2°C
Temperature stability °F	±4°F
Equipotential bonding socket	---
Display	---
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	0,7 bar, max

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[WR5000MN](#)