

WXA2

2-Channel Power Unit, 200 W (255 W)
Product no.: WXA2N



Benefits

- › Power unit, 2 channels
- › For operation with external compressed air
- › Simultaneous operation of 2 soldering tools



Technical Data

Dimensions L x W x H (mm)	174 x 154 x 135
Dimensions L x W x H (inches)	6,69 x 5,95 x 5,12
Weight (approx.) in kg	4.0
Voltage	120 V
Power	200 W (255 W)
Channels	2
Temperature range (depends on tool) °C	100 - 550
Temperature range (depends on tool) °F	200 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3, 5 mm pawl socket on back of device.
Display	255 x 128 dots / Hintergrundbeleuchtung
Air consumption l/min	20
Operating pressure in bar/psi	4,00 - 6,00 / 58 - 87
Capacity l/min	20
Vacuum	-0,6 bar

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[WXA2N](#)