

WXR3001

3-Channel Rework Station, 420 W (600 W)

Product no.: WXR3001N



Benefits

- Power unit WXR 3, 3 channels with WXHAP 200 Hot air iron, WXDP 120 Desoldering iron and WXP 65 Soldering iron





Technical Data

Dimensions L x W x H (mm)	273 x 235 x 102
Dimensions L x W x H (inches)	10,75 x 9,25 x 4,02
Weight (approx.) in kg	6.7
Voltage	120 V
Power	420 W (600 W)
Channels	3
Temperature range (depends on tool) °C	100 - 450 (550)
Temperature range (depends on tool) °F	200 - 850 (999)
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[WXR3001N](#)