

## DC Gear Motor - 430RPM (3-6V)



PID: MIKROE-4035

**DC Gear Motor - 430RPM (3-6V)** represents a brushed DC motor with a spur gearbox rated for 3-6V operational voltage range, 430RPM speed, and 60mA maximum current with a torque of 50g.cm at maximum efficiency. A great solution for fulfilling many functions initially performed by brushed DC motors in robotics, medical equipment, electric door lock, and much more.

**NOTE:** This motor can also be found in Buggy, which represents a robot rover platform expandable with sensors and transceivers thanks to its mikroBUSTM sockets. For more information, visit the [Buggy](#) product page.

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.  
ISO 14001: 2015 certification of environmental management system.  
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mikroe:](#)

[MIKROE-4035](#)