


PIN RECEPTACLES

FOR .032" - .046" DIAMETER PINS

0359

0359-0-15-XX-34-XX-10-0


Press-fit in .090 mounting hole



0358

0358-0-15-XX-34-XX-10-0


Press-fit in .090 mounting hole



0360

0360-0-15-XX-34-XX-10-0


Press-fit in .090 mounting hole



0343

0343-0-15-XX-34-XX-10-0


Press-fit in .090 mounting hole



0356

0356-0-15-XX-34-XX-10-0


Solder mount in .102 min. mounting hole
Also available on 24mm wide carrier tape:
1,100 parts per 13" reel
See page 194.11 for Tape & Reel details



6659

6659-0-15-XX-34-XX-10-0


Solder mount in .102 min. mounting hole



0347

0347-0-15-XX-34-XX-10-0


Solder mount in .120 min. mounting hole



0329

0329-0-15-XX-34-XX-10-0


Solder mount in .075 min. mounting hole. "Knock out" bottom



0814

0814-0-15-XX-34-XX-04-0


Solder mount in .082 min. mounting hole



5059

5059-0-15-XX-34-XX-04-0


Press-fit in .090 mounting hole



8360

8360-0-15-XX-34-XX-10-0


Press-fit in .087 mounting hole



9359

9359-0-15-XX-34-XX-10-0

Press-fit in .090 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#34 CONTACT (DATA ON PAGE 258)

(For alternate contact choices, see group E on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[8360-0-15-01-34-01-10-0](#) [6659-0-15-01-34-01-10-0](#) [6659-0-15-01-34-27-10-0](#) [0359-0-15-80-34-80-10-0](#) [0360-0-15-15-34-27-10-0](#) [0329-0-15-15-34-27-10-0](#) [0329-0-15-01-34-27-10-0](#) [0360-0-15-01-34-27-10-0](#) [0814-0-15-01-34-01-04-0](#) [0814-0-15-01-34-27-04-0](#) [0360-0-15-01-34-01-10-0](#) [0359-0-15-01-34-01-10-0](#) [0358-0-15-01-34-01-10-0](#) [0356-0-15-01-34-01-10-0](#) [0356-0-15-01-34-27-10-0](#) [0347-0-15-01-34-01-10-0](#) [0347-0-15-01-34-27-10-0](#) [0343-0-15-01-34-01-10-0](#) [0343-0-15-01-34-27-10-0](#) [0329-0-15-01-34-01-10-0](#) [6659-0-15-80-34-80-10-0](#) [6659-0-15-80-34-27-10-0](#) [0343-0-15-15-34-27-10-0](#) [0347-0-15-15-34-27-10-0](#) [0356-0-15-15-34-27-10-0](#) [0359-0-15-15-34-27-10-0](#) [0814-0-15-15-34-27-04-0](#) [6659-0-15-15-34-27-10-0](#) [0360-0-15-00-00-00-10-0](#) [0347-0-15-00-00-00-10-0](#) [0359-0-15-00-00-00-10-0](#) [0358-0-15-00-00-00-10-0](#) [6659-0-15-00-00-00-10-0](#) [5059-0-15-00-00-00-04-0](#) [8360-0-15-00-00-00-10-0](#) [0329-0-15-00-00-00-10-0](#) [0356-0-15-00-00-00-10-0](#) [0343-0-15-00-00-00-10-0](#) [0814-0-15-00-00-00-04-0](#) [0359-0-15-01-34-14-10-0](#) [0358-0-15-80-34-14-10-0](#) [0360-0-15-80-34-14-10-0](#) [0347-0-15-80-34-14-10-0](#) [0329-0-15-01-34-14-10-0](#) [0347-0-15-01-34-14-10-0](#) [0358-0-15-01-34-14-10-0](#) [0814-0-15-80-34-14-04-0](#) [0359-0-15-80-34-14-10-0](#) [0329-0-15-80-34-14-10-0](#) [0356-0-15-80-34-14-10-0](#) [0814-0-15-01-34-14-04-0](#) [0356-0-15-01-34-14-10-0](#) [0343-0-15-80-34-14-10-0](#) [0343-0-15-01-34-14-10-0](#) [0360-0-15-01-34-14-10-0](#) [0343-0-15-15-34-14-10-0](#) [0814-0-15-15-34-14-04-0](#) [8360-0-15-80-34-14-10-0](#) [6659-0-15-80-34-14-10-0](#) [5059-0-15-15-34-14-04-0](#) [9359-0-15-01-34-14-10-0](#) [5059-0-15-80-34-14-04-0](#) [6659-0-15-01-34-14-10-0](#) [8360-0-15-01-34-14-10-0](#) [9359-0-15-80-34-14-10-0](#) [5059-0-15-01-34-14-04-0](#)