


MALE PCB PINS

SOLDER TERMINAL TURRETS

2312

2312-X-00-XX-00-00-07-0

Swage mount in .064 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2312-1 | .031 | .053 |
| 2312-2 | .062 | .094 |
| 2312-3 | .094 | .115 |
| 2312-4 | .125 | .147 |

2308

2308-X-00-XX-00-00-07-0

Swage mount in .064 hole




| Basic Part Number | Board Thickness | Length V | Depth D |
|-------------------|-----------------|----------|---------|
| 2308-1 | .031 | .054 | .036 |
| 2308-2 | .062 | .084 | .066 |
| 2308-3 | .094 | .115 | .096 |
| 2308-4 | .125 | .147 | .126 |

2707

2707-X-00-XX-00-00-07-0

Swage mount in .120 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2707-1 | .031 | .062 |
| 2707-2 | .062 | .094 |
| 2707-3 | .094 | .125 |
| 2707-4 | .125 | .156 |

2329

2329-X-00-XX-00-00-07-0

Swage mount in .067 hole




| Basic Part Number | Board Thickness | Length V | Depth D |
|-------------------|-----------------|----------|---------|
| 2329-1 | .031 | .045 | .045 |
| 2329-2 | .062 | .094 | .062 |
| 2329-3 | .094 | .125 | .062 |
| 2329-4 | .125 | .156 | .062 |

2510

2510-X-00-XX-00-00-07-0


Swage mount in .064 hole



2513

2513-X-00-XX-00-00-07-0

Swage mount in .064 hole



| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 251X-1 | .031 | .062 |
| 251X-2 | .062 | .094 |
| 251X-3 | .094 | .125 |
| 251X-4 | .125 | .156 |

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Inches

Tolerances On: Lengths: ±.005
Diameters: ±.002
Angles: ±2°



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 44 300 μ" SILVER OVER COPPER (RoHS)
- 50 300 μ" ELECTRO-SOLDER (60/40 SnPb)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mill-Max:](#)

[2329-2-00-80-00-00-07-0](#) [2312-3-00-80-00-00-07-0](#) [2312-2-00-80-00-00-07-0](#) [2308-3-00-80-00-00-07-0](#)