

0291 0291-0-15-XX-16-XX-10-0 Hex press-fit in .067 plated thru hole	0293 0293-0-15-XX-16-XX-10-0 Press-fit in .067 mounting hole	0287 0287-0-15-XX-16-XX-10-0 Solder mount in .065 min. mounting hole	0285 0285-0-15-XX-16-XX-10-0 Solder mount in .065 min. mounting hole
0284 0284-0-15-XX-16-XX-10-0 Solder mount in .070 min. mounting hole	8114 8114-0-15-XX-16-XX-04-0 Press-fit from underside of pc board into .065 mounting hole	0407 0407-0-15-XX-16-XX-04-0 Press-fit in .066 mounting hole	0415 0415-0-15-XX-16-XX-10-0 Solder mount in .063 min. mounting hole
0303 0303-0-19-XX-16-XX-10-0 Wire Termination Press-fit in .067 mounting hole	0306 0306-0-19-XX-16-XX-10-0 Wire Termination #18 gage crimp barrel	0273 0273-0-15-XX-16-XX-10-0 Press-fit in .078 mounting hole	7520 7520-0-15-XX-16-XX-10-0 Press-fit in .066 mounting hole
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0 BASIC PART # SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: 01 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL CONTACT #16 CONTACT (DATA ON PAGE 210)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0415-0-15-01-16-14-10-0](#) [0407-0-15-01-16-14-04-0](#) [0303-0-19-01-16-14-10-0](#)