



8964




8964-0-15-XX-30-XX-04-0
Press-fit in .057 mounting hole

5342



5342-0-15-XX-35-XX-10-0
Solder mount in .051 min. mounting hole


8857



8857-X-15-XX-32-XX-04-0
Press-fit in .057 mounting hole

Basic Part Number	Length A
8857-0	.311
8857-1	.448
8857-2	.589
8857-3	.731
8857-4	.871


8862/8877



88XX-0-15-XX-30-XX-04-0
Press-fit in .056 mounting hole

Basic Part Number	Length A
8862-0	.300
8877-0	.350

1334



1334-0-15-XX-30-XX-04-0
Press-fit in .057 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#30, #32 or #35 CONTACT (DATA ON PAGES 208 & 209)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[5342-0-15-01-35-14-10-0](#) [8857-2-15-01-32-14-04-0](#) [8964-0-15-01-30-14-04-0](#) [8857-3-15-01-32-14-04-0](#) [8857-0-15-01-32-14-04-0](#) [8857-1-15-01-32-14-04-0](#) [8877-0-15-01-30-14-04-0](#) [8862-0-15-01-30-14-04-0](#) [8857-4-15-01-32-14-04-0](#)