



0401/6401



Basic Part Number	Length A
0401-0	.340
6401-0	.540

X401-0-15-XX-47-XX-04-0
Press-fit in .064 mounting hole


1303/8303



Basic Part Number	Length A
1303-0	.125
8303-0	.800

X303-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole


4094/4095



Basic Part Number	Length A
4094-0	.260
4095-0	.635

409X-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole

8806



8806-0-18-XX-47-XX-10-0
Surface mount
Also available on 12mm wide carrier
tape: 4,000 parts per 13" reel.
Order as: 8806-0-67-XX-47-XX-10-0

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 15 - XX - 47 - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
15 10 μ " GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
14 10 μ " GOLD OVER NICKEL
27 30 μ " GOLD OVER NICKEL

CONTACT

#47 CONTACT (DATA ON PAGE 211)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0401-0-15-01-47-14-04-0](#) [6401-0-15-01-47-14-04-0](#) [4095-0-15-01-47-14-04-0](#) [4094-0-15-01-47-14-04-0](#) [8303-0-15-01-47-14-04-0](#)