



1802/3802/4030/8866



Basic Part Number	Length A
1802-0	.125
3802-0	.165
8866-0	.775
4030-0	.815

XXXX-0-15-XX-43-XX-04-0
Press-fit in .057 mounting hole


1803/1805



Basic Part Number	Length A
1803-0	.145
1805-0	.213

180X-0-15-XX-43-XX-04-0
Press-fit in .057 mounting hole


1804/1806



Basic Part Number	Length A
1804-0	.080
1806-0	.115


180X-0-15-XX-43-XX-04-0
Press-fit in .057 mounting hole

1808




1808-0-15-XX-43-XX-04-0
Press-fit in .057 mounting hole

1807




1807-0-15-XX-43-XX-04-0
Press-fit in .057 mounting hole

8830




8830-0-15-XX-22-XX-10-0
Solder mount in .057 min. mounting hole

9363




9363-0-15-XX-35-XX-10-0
Solder mount in .057 min. mounting hole

4622



4622-0-15-XX-30-XX-10-0
Hex press-fit in .053 plated thru hole

6252



6252-0-15-XX-32-XX-10-0
Hex press-fit in .057 plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - 0 - 1X - XX - XX - XX - XX - 0

BASIC PART # →
SPECIFY SHELL FINISH: →
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH: →
02 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#22, #30, #32, #35 or #43 CONTACT (DATA ON PAGES 207, 208 & 209)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1808-0-15-01-43-14-04-0](#) [1804-0-15-01-43-14-04-0](#) [1803-0-15-01-43-14-04-0](#) [1802-0-15-01-43-14-04-0](#) [9363-0-15-01-35-14-10-0](#) [4030-0-15-01-43-14-04-0](#) [6252-0-15-01-32-14-10-0](#) [8866-0-15-01-43-14-04-0](#)