



8838



8838-0-15-XX-34-XX-10-0

Solder mount in .086 min.
mounting hole


3100



3100-0-15-XX-34-XX-10-0

Solder mount in .074 min.
mounting hole


8853



8853-0-15-XX-34-XX-10-0

Press-fit in .071 mounting hole


6800



6800-0-15-XX-34-XX-04-0

Solder mount in .080 min.
mounting hole


8206



8206-0-15-XX-34-XX-10-0

Surface mount

0739



0739-0-15-XX-34-XX-10-0

Hex press-fit in .078±.002
plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES

TOLERANCES ON:

LENGTHS: $\pm .005$

DIAMETERS: $\pm .002$

DIAMETERS: $\pm .002$
 ANGLES: $\pm .002^\circ$

ORDER CODE: XXXX - 0 - 15 - XX - 34 - XX - 10 - 0

BASIC PART # _____ ↗

SPECIFY SHELL FINISH:

01 200μ" TIN/LEAD OVER NICKEL

15 10 μ " GOLD OVER NICKEL

SPECIFY CONTACT FINISH:

01 200μ" TIN/LEAD OVER NICKEL

14 10μ" GOLD OVER NICKEL

27 30 μ " GOLD OVER NICKEL

CONTACT

#34 CONTACT (DATA ON PAGE 212)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3100-0-15-01-34-14-10-0](#) [8838-0-15-01-34-14-10-0](#)