


0327/0351/0373




Basic Part Number	Length L	Depth N
0327-0	.206	.180
0351-0	.226	.200
0373-0	.270	.241

03XX-0-15-XX-34-XX-10-0

Solder mount in .075 min. mounting hole


0328



0328-0-15-XX-34-XX-10-0

Hex press-fit in .079 plated thru hole


0334



0334-0-15-XX-34-XX-10-0

Hex press-fit in .079 plated thru hole


0312



0312-0-15-XX-34-XX-10-0

Solder mount in .075 min. mounting hole


0333



0333-0-42-XX-34-XX-10-0

Press-fit in .076 mounting hole


0357



0357-0-15-XX-34-XX-10-0

Press-fit in .078 mounting hole


0317



0317-0-15-XX-34-XX-10-0

Solder mount in .091 min. mounting hole


0340



0340-0-15-XX-34-XX-10-0

Solder mount in .087 min. mounting hole


0345



0345-0-15-XX-34-XX-10-0

Press-fit in .089 mounting hole


0316



0316-0-15-XX-34-XX-10-0

Solder mount in .087 min. mounting hole

0314



0314-0-15-XX-34-XX-10-0

Solder mount in .087 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - 34 - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200μ" TIN/LEAD OVER NICKEL

15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:

01 200μ" TIN/LEAD OVER NICKEL

14 10μ" GOLD OVER NICKEL

27 30μ" GOLD OVER NICKEL

CONTACT

#34 CONTACT (DATA ON PAGE 212)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0333-0-42-01-34-14-10-0](#) [0340-0-15-01-34-14-10-0](#) [0357-0-15-01-34-14-10-0](#) [0345-0-15-01-34-14-10-0](#) [0316-0-15-01-34-14-10-0](#) [0357-0-15-15-34-14-10-0](#)