



0444



Basic Part Number	# of Wraps	Length A
0444-1	1	6,6
0444-2	2	9,4
0444-3	3	12,83

0444-X-17-XX-30-XX-02-0
Press-fit in 1,42 mounting hole


0445/0446



Basic Part Number	# of Wraps	Length A
0446-2	2	9,4
0445-3	3	12,83

044X-X-17-XX-30-XX-02-0
Press-fit in 1,42 mounting hole


2601⇒2603



Basic Part Number	# of Wraps	Length A
2601-0	1	5,89
2602-0	2	8,89
2603-0	3	11,89

260X-X-17-XX-30-XX-02-0
Press-fit in 1,45 mounting hole

1047



1047-3-17-XX-30-XX-02-0
Press-fit in 1,42 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

PART MANUFACTURED IN
INCHES, METRIC FOR REF ONLY

TOLERANCES ON:
LENGTHS: ± 0,13
DIAMETERS: ± 0,05
ANGLES: ± 2°

ORDER CODE: XXXX - X - 17 - XX - 30 - XX - 02 - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 5,08µm TIN/LEAD OVER NICKEL

80 5,08µm TIN OVER NICKEL

15 0,25µm GOLD OVER NICKEL

SPECIFY CONTACT FINISH:

02 2,54µm TIN/LEAD OVER NICKEL

84 2,54µm TIN OVER NICKEL

27 0,76µm GOLD OVER NICKEL

CONTACT

#30 CONTACT (DATA ON PAGE 208)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0446-2-17-01-30-27-02-0](#) [0446-2-17-01-30-02-02-0](#) [0446-2-17-80-30-84-02-0](#) [0446-2-17-80-30-27-02-0](#) [0446-2-17-15-30-27-02-0](#)