

170...001 173...001

- Series 170 & 173 DIL headers are equipped with turret heads for wiring applications.
- Series 170 terminations are pluggable 0,51 dia. solder tails MM #0700, See page 183 for details. Series 173 terminations are three level wraposts MM #0730. See page 195 for details.
- Insulators are high temperature thermoplastic.

Total number of pins				Quantity per tube	Ordering Information					
	A	B	C		Solder Tail		3 Level Wrapost			
10	12,6	5,08	7,6	41	170-XX-210-00-001000	173-10-210-00-001000		RoHS 2002/95/EC For RoHS compliance select ◇ plating code. For Electrical, Mechanical & Enviromental Data, See pg. 4 XX=Plating Code See Below		
4	5,0	7,62	10,1	102	170-XX-304-00-001000	173-10-304-00-001000				
6	7,6	7,62	10,1	67	170-XX-306-00-001000	173-10-306-00-001000				
8	10,1	7,62	10,1	50	170-XX-308-00-001000	173-10-308-00-001000				
10	12,6	7,62	10,1	40	170-XX-310-00-001000	173-10-310-00-001000				
14	17,7	7,62	10,1	28	170-XX-314-00-001000	173-10-314-00-001000				
16	20,3	7,62	10,1	25	170-XX-316-00-001000	173-10-316-00-001000				
18	22,8	7,62	10,1	22	170-XX-318-00-001000	173-10-318-00-001000				
20	25,3	7,62	10,1	20	170-XX-320-00-001000	173-10-320-00-001000				
22	27,8	7,62	10,1	18	170-XX-322-00-001000	173-10-322-00-001000				
24	30,4	7,62	10,1	16	170-XX-324-00-001000	173-10-324-00-001000				
28	35,5	7,62	10,1	14	170-XX-328-00-001000	173-10-328-00-001000				
20	25,4	10,16	12,7	20	170-XX-420-00-001000	173-10-420-00-001000				
22	27,8	10,16	12,7	18	170-XX-422-00-001000	173-10-422-00-001000				
24	30,4	10,16	12,7	16	170-XX-424-00-001000	173-10-424-00-001000				
28	35,5	10,16	12,7	14	170-XX-428-00-001000	173-10-428-00-001000				
32	40,6	10,16	12,7	12	170-XX-432-00-001000	173-10-432-00-001000				
24	30,4	15,24	17,7	16	170-XX-624-00-001000	173-10-624-00-001000				
28	35,5	15,24	17,7	14	170-XX-628-00-001000	173-10-628-00-001000				
32	40,6	15,24	17,7	12	170-XX-632-00-001000	173-10-632-00-001000				
36	45,7	15,24	17,7	11	170-XX-636-00-001000	173-10-636-00-001000				
40	50,8	15,24	17,7	10	170-XX-640-00-001000	173-10-640-00-001000				
42	53,3	15,24	17,7	9	170-XX-642-00-001000	173-10-642-00-001000				
48	60,9	15,24	17,7	8	170-XX-648-00-001000	173-10-648-00-001000				
50	63,5	15,24	17,7	8	170-XX-650-00-001000	173-10-650-00-001000				
52	66,0	15,24	17,7	7	170-XX-652-00-001000	173-10-652-00-001000				
50	63,5	22,86	25,3	8	170-XX-950-00-001000	173-10-950-00-001000				
52	66,0	22,86	25,3	7	170-XX-952-00-001000	173-10-952-00-001000				
64	81,2	22,86	25,3	6	170-XX-964-00-001000	173-10-964-00-001000				
SPECIFY PLATING CODE XX=					10◇	90	40◇			
Pin Plating					0,25µm Au	5,08µm Sn/Pb	5,08µm Sn			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[173-10-964-00-001000](#) [173-10-952-00-001000](#) [173-10-950-00-001000](#) [173-10-652-00-001000](#) [173-10-650-00-001000](#) [173-10-648-00-001000](#) [173-10-642-00-001000](#) [173-10-640-00-001000](#) [173-10-636-00-001000](#) [173-10-632-00-001000](#) [173-10-628-00-001000](#) [173-10-624-00-001000](#) [173-10-432-00-001000](#) [173-10-428-00-001000](#) [173-10-424-00-001000](#) [173-10-422-00-001000](#) [173-10-420-00-001000](#) [173-10-328-00-001000](#) [173-10-324-00-001000](#) [173-10-322-00-001000](#) [173-10-320-00-001000](#) [173-10-318-00-001000](#) [173-10-316-00-001000](#) [173-10-314-00-001000](#) [173-10-310-00-001000](#) [173-10-308-00-001000](#) [173-10-306-00-001000](#) [173-10-304-00-001000](#) [170-90-964-00-001000](#) [170-90-952-00-001000](#) [170-90-950-00-001000](#) [170-90-652-00-001000](#) [170-90-650-00-001000](#) [170-90-648-00-001000](#) [170-90-642-00-001000](#) [170-90-640-00-001000](#) [170-90-636-00-001000](#) [170-90-632-00-001000](#) [170-90-628-00-001000](#) [170-90-624-00-001000](#) [170-90-432-00-001000](#) [170-90-428-00-001000](#) [170-90-424-00-001000](#) [170-90-422-00-001000](#) [170-90-420-00-001000](#) [170-90-328-00-001000](#) [170-90-324-00-001000](#) [170-90-322-00-001000](#) [170-90-320-00-001000](#) [170-90-318-00-001000](#) [170-90-316-00-001000](#) [170-90-314-00-001000](#) [170-90-310-00-001000](#) [170-90-308-00-001000](#) [170-90-306-00-001000](#) [170-90-304-00-001000](#) [170-90-210-00-001000](#) [170-10-964-00-001000](#) [170-10-952-00-001000](#) [170-10-950-00-001000](#) [170-10-652-00-001000](#) [170-10-650-00-001000](#) [170-10-648-00-001000](#) [170-10-642-00-001000](#) [170-10-640-00-001000](#) [170-10-636-00-001000](#) [170-10-632-00-001000](#) [170-10-624-00-001000](#) [170-10-432-00-001000](#) [170-10-428-00-001000](#) [170-10-424-00-001000](#) [170-10-422-00-001000](#) [170-10-420-00-001000](#) [170-10-328-00-001000](#) [170-10-324-00-001000](#) [170-10-322-00-001000](#) [170-10-320-00-001000](#) [170-10-318-00-001000](#) [170-10-316-00-001000](#) [170-10-314-00-001000](#) [170-10-310-00-001000](#) [170-10-308-00-001000](#) [170-10-306-00-001000](#) [170-10-304-00-001000](#) [170-10-210-00-001000](#) [170-40-964-00-001000](#) [170-40-952-00-001000](#) [170-40-950-00-001000](#) [170-40-652-00-001000](#) [170-40-650-00-001000](#) [170-40-648-00-001000](#) [170-40-642-00-001000](#) [170-40-640-00-001000](#) [170-40-636-00-001000](#) [170-40-632-00-001000](#) [170-40-628-00-001000](#) [170-40-624-00-001000](#) [170-40-432-00-001000](#) [170-40-428-00-001000](#) [170-40-424-00-001000](#)